

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P224651

Luminaire Tested: **LSSQ2B05FL409040D010 2LBDLC*MW**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P224651
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P14835)
Test Lab: INNOVATION CENTER (G1)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSSQ2B05FL409040D010 2LBDLC*MW
Description: 500 Lumen, 2inch Portfolio LED Cylinder
FLOOD OPTIC
LENSED CAST ROUND TRIM WITH MATTE WHITE FINISH
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 608.1 lumens
Efficiency: N/A
Efficacy: 83.3 lumens/watt
Spacing Criteria (0/90/45): 0.61 / 0.61 / 0.59
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 7.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P224651

CATALOG NUMBER: LSSQ2B05FL409040D010 2LBDLC*MW

Luminous Intensity Polar Plot





TEST NUMBER: P224651

CATALOG NUMBER: LSSQ2B05FL409040D010 2LBDLC*MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	99	98	97	95		
2	110	106	102	99	108	104	101	98	101	98	96	98	96	94	95	94	92	91		
3	105	100	96	93	104	99	95	92	96	93	90	94	91	89	92	90	88	86		
4	101	95	90	87	100	94	90	86	92	88	85	90	87	85	88	86	84	82		
5	97	91	86	82	96	90	85	82	88	84	81	86	83	80	85	82	80	79		
6	94	86	82	78	93	86	81	78	84	80	77	83	79	77	82	79	76	75		
7	90	83	78	74	89	82	77	74	81	77	74	80	76	73	79	76	73	72		
8	87	79	74	71	86	79	74	71	78	74	71	77	73	70	76	73	70	69		
9	84	76	71	68	83	76	71	68	75	71	68	74	70	67	73	70	67	66		
10	81	73	68	65	80	73	68	65	72	68	65	71	68	65	71	67	65	64		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	550419
5°	540390
10°	480403
15°	377832
20°	251404
25°	144329
30°	72905
35°	34283
40°	13804
45°	6847
50°	3736
55°	2634
60°	2402
65°	1466
70°	1812
75°	1197
80°	1785
85°	0



TEST NUMBER: P224651

CATALOG NUMBER: LSSQ2B05FL409040D010 2LBDLC*MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	127.3	20.9
10°-20°	255.2	42.0
20°-30°	158.8	26.1
30°-40°	48.8	8.0
40°-50°	10.7	1.8
50°-60°	3.8	0.6
60°-70°	1.9	0.3
70°-80°	1.2	0.2
80°-90°	0.3	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	541.3	89.0
0°-40°	590.1	97.0
0°-60°	604.6	99.4
0°-90°	608.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	608.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1421	
5°	1390	127
15°	942	255
25°	338	159
35°	72	49
45°	12	11
55°	4	4
65°	2	2
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P224651

CATALOG NUMBER: LSSQ2B05FL409040D010 2LBDLC*MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	1421.0
2.5°	1414.8
5°	1389.8
7.5°	1326.7
10°	1221.4
12.5°	1095.0
15°	942.2
17.5°	775.2
20°	609.9
22.5°	462.5
25°	337.7
27.5°	237.9
30°	163.0
32.5°	110.0
35°	72.5
37.5°	43.7
40°	27.3
42.5°	18.7
45°	12.5
47.5°	8.6
50°	6.2
52.5°	5.5
55°	3.9
57.5°	3.1
60°	3.1
62.5°	2.3
65°	1.6
67.5°	1.6
70°	1.6
72.5°	1.6
75°	0.8
77.5°	0.8
80°	0.8
82.5°	0.8
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)