

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P265050

Luminaire Tested: **LD2B20D010 EU2B2010SP159035 2LBLC*MB**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P265050
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1711-432-2)
Test Lab: INNOVATION CENTER(G3)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD2B20D010 EU2B2010SP159035 2LBLC*MB
Description: 2000 Lumen, 2inch Portfolio LED Downlight
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1306.0 lumens
Efficiency: N/A
Efficacy: 62.5 lumens/watt
Spacing Criteria (0/90/45): 0.31 / 0.31 / 0.32
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 20.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P265050

CATALOG NUMBER: LD2B20D010 EU2B2010SP159035 2LBLC*MB

Luminous Intensity Polar Plot





TEST NUMBER: P265050

CATALOG NUMBER: LD2B20D010 EU2B2010SP159035 2LBLC*MB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10		50	30	10			50	30	10			0
RCR																				
0	119	119	119	119	116	116	116	116		111	111	111			106	106	106			100
1	115	113	111	110	113	111	110	108		107	106	105			104	103	102			97
2	112	108	106	103	110	107	104	102		104	102	100			101	99	98			94
3	109	104	101	98	107	103	100	97		100	98	96			98	96	94			92
4	106	100	97	94	104	99	96	93		97	95	92			96	93	91			89
5	103	97	93	91	101	96	93	90		95	92	89			93	91	89			87
6	100	94	90	88	99	94	90	87		92	89	87			91	88	86			85
7	98	92	88	85	97	91	88	85		90	87	85			89	86	84			83
8	95	89	86	83	94	89	85	83		88	85	82			87	84	82			81
9	93	87	83	81	92	87	83	81		86	83	81			85	82	80			79
10	91	85	82	79	91	85	81	79		84	81	79			84	81	79			78

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	4610466
5°	3752432
10°	2026986
15°	808185
20°	324045
25°	155198
30°	80440
35°	42521
40°	23572
45°	14582
50°	10055
55°	6709
60°	5131
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P265050

CATALOG NUMBER: LD2B20D010 EU2B2010SP159035 2LBLC*MB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	609.3	46.7
10°-20°	480.8	36.8
20°-30°	141.8	10.9
30°-40°	47.2	3.6
40°-50°	17.7	1.4
50°-60°	7.8	0.6
60°-70°	1.3	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1231.9	94.3
0°-40°	1279.1	97.9
0°-60°	1304.7	99.9
0°-90°	1306.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1306.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	9345	
5°	7577	609
15°	1582	481
25°	285	142
35°	71	47
45°	21	18
55°	8	8
65°	0	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P265050

CATALOG NUMBER: LD2B20D010 EU2B2010SP159035 2LBLC*MB

CANDELA DISTRIBUTION (FULL):

	0°
0°	9345.0
2.5°	8968.3
5°	7576.9
7.5°	5837.7
10°	4046.1
12.5°	2589.3
15°	1582.3
17.5°	965.1
20°	617.2
22.5°	413.2
25°	285.1
27.5°	201.4
30°	141.2
32.5°	99.4
35°	70.6
37.5°	49.7
40°	36.6
42.5°	28.8
45°	20.9
47.5°	18.3
50°	13.1
52.5°	10.5
55°	7.8
57.5°	7.8
60°	5.2
62.5°	2.6
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)