

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P224336

Luminaire Tested: **LSSQWM2B05FL409040D010 2LBDDELETEC*MMS**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P224336
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P14831)
Test Lab: INNOVATION CENTER (G1)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSSQWM2B05FL409040D010 2LBDDELETEC*MMS
Description: 500 Lumen, 2inch Portfolio LED Cylinder
FLOOD OPTIC
SQUARE CAST TRIM WITH MATTE METALLIC SILVER
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 624.8 lumens
Efficiency: N/A
Efficacy: 85.6 lumens/watt
Spacing Criteria (0/90/45): 0.61 / 0.61 / 0.59
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 7.3
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P224336

CATALOG NUMBER: LSSQWM2B05FL409040D010 2LBDDELETEC*MMS

Luminous Intensity Polar Plot





TEST NUMBER: P224336

CATALOG NUMBER: LSSQWM2B05FL409040D010 2LBDDELETEC*MMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	114	112	110	108	112	110	108	106	106	104	103		102	101	100		99
2	110	106	102	100	108	104	101	99	101	99	96		98	96	94		95
3	106	100	96	93	104	99	95	92	97	93	91		94	92	89		92
4	102	95	91	87	100	94	90	87	92	89	86		90	87	85		89
5	98	91	86	83	96	90	86	82	88	85	82		87	83	81		85
6	94	87	82	78	93	86	82	78	85	81	78		83	80	77		82
7	91	83	78	75	89	82	78	75	81	77	74		80	77	74		79
8	87	80	75	71	86	79	75	71	78	74	71		77	73	71		76
9	84	76	72	68	83	76	71	68	75	71	68		74	71	68		74
10	81	74	69	66	81	73	69	66	72	68	65		72	68	65		71

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	568740
5°	557809
10°	495506
15°	391025
20°	260802
25°	150099
30°	76036
35°	35654
40°	14613
45°	6573
50°	3375
55°	2161
60°	1240
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P224336

CATALOG NUMBER: LSSQWM2B05FL409040D010 2LBDDELETEC*MMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	131.3	21.0
10°-20°	263.5	42.2
20°-30°	165.0	26.4
30°-40°	51.1	8.2
40°-50°	10.5	1.7
50°-60°	2.9	0.5
60°-70°	0.4	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	559.8	89.6
0°-40°	610.9	97.8
0°-60°	624.4	99.9
0°-90°	624.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	624.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1468	
5°	1435	131
15°	975	264
25°	351	165
35°	75	51
45°	12	11
55°	3	3
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P224336

CATALOG NUMBER: LSSQWM2B05FL409040D010 2LBDDELETEC*MMS

CANDELA DISTRIBUTION (FULL):

	0°
0°	1468.3
2.5°	1461.1
5°	1434.6
7.5°	1367.3
10°	1259.8
12.5°	1127.5
15°	975.1
17.5°	799.5
20°	632.7
22.5°	481.1
25°	351.2
27.5°	247.0
30°	170.0
32.5°	113.9
35°	75.4
37.5°	47.3
40°	28.9
42.5°	18.4
45°	12.0
47.5°	8.0
50°	5.6
52.5°	4.0
55°	3.2
57.5°	2.4
60°	1.6
62.5°	0.8
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)