

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P264378

Luminaire Tested: **LD2B20D010 EU2B2010SP159035 2LBSQC*MW**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P264378
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1805-787-1)
Test Lab: INNOVATION CENTER(G2)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD2B20D010 EU2B2010SP159035 2LBSQC*MW
Description: 2000 Lumen, 2inch Portfolio LED Downlight
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1327.1 lumens
Efficiency: N/A
Efficacy: 63.5 lumens/watt
Spacing Criteria (0/90/45): 0.28 / 0.28 / 0.28
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 20.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P264378

CATALOG NUMBER: LD2B20D010 EU2B2010SP159035 2LBSQC*MW

Luminous Intensity Polar Plot





TEST NUMBER: P264378

CATALOG NUMBER: LD2B20D010 EU2B2010SP159035 2LBSQC*MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10			50	30	10			0
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111			106	106	106			100
1	116	114	112	111		113	112	110	109		108	107	106			104	103	102			98
2	113	109	107	105		111	108	106	104		105	103	101			102	101	99			96
3	110	106	103	100		108	105	102	100		102	100	98			100	98	97			94
4	107	103	99	97		106	102	99	96		100	97	95			98	96	94			92
5	105	100	97	94		104	99	96	94		98	95	93			96	94	92			90
6	103	98	94	92		102	97	94	91		96	93	91			95	92	90			89
7	101	95	92	90		100	95	92	89		94	91	89			93	90	89			87
8	99	93	90	88		98	93	90	88		92	89	87			91	89	87			86
9	97	92	88	86		96	91	88	86		91	88	86			90	87	86			85
10	95	90	87	85		95	90	87	85		89	86	85			89	86	84			83

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	6261600
5°	5018975
10°	2190553
15°	678859
20°	236629
25°	104518
30°	47341
35°	24633
40°	14040
45°	6628
50°	4145
55°	2322
60°	1381
65°	1634
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P264378

CATALOG NUMBER: LD2B20D010 EU2B2010SP159035 2LBSQC*MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	769.6	58.0
10°-20°	421.5	31.8
20°-30°	96.1	7.2
30°-40°	27.6	2.1
40°-50°	8.5	0.6
50°-60°	2.6	0.2
60°-70°	1.2	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1287.1	97.0
0°-40°	1314.8	99.1
0°-60°	1325.8	99.9
0°-90°	1327.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1327.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	12692	
5°	10134	770
15°	1329	421
25°	192	96
35°	41	28
45°	10	9
55°	3	3
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P264378

CATALOG NUMBER: LD2B20D010 EU2B2010SP159035 2LBSQC*MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	12691.7
1°	12533.7
2°	12205.5
3°	11696.2
4°	10996.3
5°	10134.3
6°	9077.6
7°	7896.9
8°	6664.5
9°	5471.6
10°	4372.6
11°	3442.6
12°	2709.9
13°	2132.5
14°	1684.5
15°	1329.1
16°	1048.6
17°	834.8
18°	671.4
19°	546.1
20°	450.7
22.5°	291.4
25°	192.0
26°	162.1
27°	137.5
28°	115.8
29°	96.7
30°	83.1
32.5°	57.2
35°	40.9
37.5°	30.0
40°	21.8
42.5°	15.0
45°	9.5
47.5°	6.8
50°	5.4
52.5°	4.1
55°	2.7
57.5°	1.4
60°	1.4
62.5°	1.4
65°	1.4
67.5°	1.4



TEST NUMBER: P264378

CATALOG NUMBER: LD2B20D010 EU2B2010SP159035 2LBSQC*MW

CANDELA DISTRIBUTION (continued):

	0°
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







70°	0.0
72.5°	0.0



(END OF REPORT)