

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P225218

Luminaire Tested: **LSSQWM2B05FL409040D010 2LBDDELETELC*MB**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P225218
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P14838)
Test Lab: INNOVATION CENTER (G1)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSSQWM2B05FL409040D010 2LBDDELETELC*MB
Description: 500 Lumen, 2inch Portfolio LED Cylinder
FLOOD OPTIC
LENSED SQUARE CAST TRIM WITH MATTE BLACK FINISH
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 573.0 lumens
Efficiency: N/A
Efficacy: 78.5 lumens/watt
Spacing Criteria (0/90/45): 0.6 / 0.61 / 0.59
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 7.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P225218

CATALOG NUMBER: LSSQWM2B05FL409040D010 2LBDDELETELC*MB

Luminous Intensity Polar Plot





TEST NUMBER: P225218

CATALOG NUMBER: LSSQWM2B05FL409040D010 2LBDDELETELC*MB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10			50	30	10			50
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111			106	106	106			102
1	115	112	110	108		112	110	108	107		106	105	103			102	101	100			99
2	110	106	103	100		108	105	102	99		101	99	97			98	97	95			96
3	106	101	97	94		104	99	96	93		97	94	91			95	92	90			92
4	102	96	92	88		100	95	91	88		93	89	87			91	88	86			89
5	98	92	87	84		97	91	86	83		89	85	82			88	84	82			86
6	95	88	83	79		93	87	82	79		86	82	79			84	81	78			83
7	91	84	79	76		90	83	79	76		82	78	75			81	78	75			80
8	88	81	76	73		87	80	76	73		79	75	72			78	75	72			77
9	85	78	73	70		84	77	73	70		76	72	69			75	72	69			75
10	82	75	70	67		82	74	70	67		74	70	67			73	69	67			72

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	539999	539999	539999
5°	529308	538407	532652
10°	471042	481150	476234
15°	363917	377070	370493
20°	240068	245221	241346
25°	130952	139970	131636
30°	58950	65212	56490
35°	25440	26197	23218
40°	10669	11023	9860
45°	4273	4711	4711
50°	1868	2350	2350
55°	1081	1081	1553
60°	620	620	620
65°	0	0	0
70°	0	0	0
75°	0	0	0
80°	0	0	0
85°	0	0	0



TEST NUMBER: P225218

CATALOG NUMBER: LSSQWM2B05FL409040D010 2LBDDELETEL*MB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	126.0	22.0
10°-20°	250.8	43.8
20°-30°	148.2	25.9
30°-40°	38.6	6.7
40°-50°	7.6	1.3
50°-60°	1.7	0.3
60°-70°	0.1	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	525.0	91.6
0°-40°	563.6	98.3
0°-60°	572.9	100.0
0°-90°	573.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	573.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1394	1394	1394	1394	1394	
5°	1361	1372	1385	1375	1370	125
15°	908	928	940	926	924	246
25°	306	316	328	315	308	144
35°	54	56	55	55	49	38
45°	8	9	9	9	9	7
55°	2	2	2	2	2	2
65°	0	0	0	0	0	0
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	0	0	0	0	0	0



TEST NUMBER: P225218

CATALOG NUMBER: LSSQWM2B05FL409040D010 2LBDDELETELC*MB

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1394.1	1394.1	1394.1	1394.1	1394.1
2.5°	1379.2	1393.3	1402.6	1394.8	1386.3
5°	1361.3	1372.2	1384.7	1375.3	1369.9
7.5°	1297.4	1313.7	1323.1	1318.4	1309.8
10°	1197.6	1210.0	1223.3	1218.6	1210.8
12.5°	1065.8	1083.0	1095.4	1084.5	1086.1
15°	907.5	927.8	940.3	926.2	923.9
17.5°	739.9	755.5	764.1	755.5	749.3
20°	582.4	591.8	594.9	591.0	585.5
22.5°	430.4	440.5	449.9	440.5	433.5
25°	306.4	316.5	327.5	315.0	308.0
27.5°	206.6	212.8	222.2	210.5	200.4
30°	131.8	138.8	145.8	137.2	126.3
32.5°	83.4	88.1	88.9	87.3	78.0
35°	53.8	56.1	55.4	54.6	49.1
37.5°	34.3	34.3	35.1	34.3	31.2
40°	21.1	22.6	21.8	21.1	19.5
42.5°	12.5	14.0	13.3	13.3	12.5
45°	7.8	9.4	8.6	8.6	8.6
47.5°	5.5	6.2	5.5	5.5	6.2
50°	3.1	3.9	3.9	3.9	3.9
52.5°	2.3	2.3	2.3	2.3	3.1
55°	1.6	1.6	1.6	1.6	2.3
57.5°	1.6	1.6	0.8	0.8	1.6
60°	0.8	0.8	0.8	0.8	0.8
62.5°	0.8	0.0	0.0	0.0	0.8
65°	0.0	0.0	0.0	0.0	0.0
67.5°	0.0	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180° - - 45°-225° - - - 90°-270°







(END OF REPORT)