

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P265055

Luminaire Tested: **LD2B20D010 EU2B2010SP159035 2LBSQLC*MMS**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P265055
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1711-432-2)
Test Lab: INNOVATION CENTER(G3)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD2B20D010 EU2B2010SP159035 2LBSQLC*MMS
Description: 2000 Lumen, 2inch Portfolio LED Downlight
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1318.0 lumens
Efficiency: N/A
Efficacy: 63.1 lumens/watt
Spacing Criteria (0/90/45): 0.31 / 0.31 / 0.32
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 20.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P265055

CATALOG NUMBER: LD2B20D010 EU2B2010SP159035 2LBSQLC*MMS

Luminous Intensity Polar Plot





TEST NUMBER: P265055

CATALOG NUMBER: LD2B20D010 EU2B2010SP159035 2LBSQLC*MMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	115	113	111	110	113	111	110	108	107	106	105		104	103	102		100
2	112	108	106	103	110	107	104	102	104	102	100		101	99	98		98
3	109	104	101	98	107	103	100	97	100	98	96		98	96	94		96
4	105	100	97	94	104	99	96	93	97	95	92		96	93	91		94
5	103	97	93	91	101	96	93	90	95	92	89		93	91	89		92
6	100	94	90	88	99	94	90	87	92	89	87		91	88	86		90
7	98	92	88	85	97	91	88	85	90	87	85		89	86	84		88
8	95	89	86	83	94	89	85	83	88	85	82		87	84	82		86
9	93	87	83	81	92	87	83	81	86	83	81		85	82	80		85
10	91	85	82	79	91	85	81	79	84	81	79		84	81	79		83

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	4652796
5°	3786901
10°	2045622
15°	815642
20°	327038
25°	156614
30°	81180
35°	42943
40°	23829
45°	14722
50°	10131
55°	6795
60°	5230
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P265055

CATALOG NUMBER: LD2B20D010 EU2B2010SP159035 2LBSQLC*MMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	614.9	46.7
10°-20°	485.2	36.8
20°-30°	143.1	10.9
30°-40°	47.6	3.6
40°-50°	17.9	1.4
50°-60°	7.9	0.6
60°-70°	1.3	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1243.2	94.3
0°-40°	1290.9	97.9
0°-60°	1316.7	99.9
0°-90°	1318.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1318.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	9431	
5°	7646	615
15°	1597	485
25°	288	143
35°	71	48
45°	21	18
55°	8	8
65°	0	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P265055

CATALOG NUMBER: LD2B20D010 EU2B2010SP159035 2LBSQLC*MMS

CANDELA DISTRIBUTION (FULL):

	0°
0°	9430.8
2.5°	9050.7
5°	7646.5
7.5°	5891.3
10°	4083.3
12.5°	2613.1
15°	1596.9
17.5°	974.0
20°	622.9
22.5°	417.0
25°	287.7
27.5°	203.2
30°	142.5
32.5°	100.3
35°	71.3
37.5°	50.1
40°	37.0
42.5°	29.0
45°	21.1
47.5°	18.5
50°	13.2
52.5°	10.6
55°	7.9
57.5°	7.9
60°	5.3
62.5°	2.6
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)