

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P265054

Luminaire Tested: **LD2B20D010 EU2B2010SP159035 2LBSQLC*MW**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P265054
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1711-432-2)
Test Lab: INNOVATION CENTER(G3)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD2B20D010 EU2B2010SP159035 2LBSQLC*MW
Description: 2000 Lumen, 2inch Portfolio LED Downlight
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1438.0 lumens
Efficiency: N/A
Efficacy: 68.8 lumens/watt
Spacing Criteria (0/90/45): 0.31 / 0.31 / 0.32
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 20.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P265054

CATALOG NUMBER: LD2B20D010 EU2B2010SP159035 2LBSQLC*MW

Luminous Intensity Polar Plot





TEST NUMBER: P265054

CATALOG NUMBER: LD2B20D010 EU2B2010SP159035 2LBSQLC*MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	115	113	111	110	113	111	110	108	107	106	105		104	103	102		100
2	112	108	106	103	110	107	104	102	104	102	100		101	99	98		98
3	109	104	101	98	107	103	100	97	100	98	96		98	96	94		96
4	105	100	97	94	104	99	96	93	97	95	92		96	93	91		94
5	103	97	93	91	101	96	93	90	95	92	89		93	91	89		92
6	100	94	90	88	99	94	90	87	92	89	87		91	88	86		90
7	98	92	88	85	97	91	88	85	90	87	85		89	86	84		88
8	95	89	86	83	94	89	85	83	88	85	82		87	84	82		86
9	93	87	83	81	92	87	83	81	86	83	81		85	82	80		85
10	91	85	82	79	91	85	81	79	84	81	79		84	81	79		83

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	5076446
5°	4131692
10°	2231833
15°	889907
20°	356807
25°	170876
30°	88586
35°	46858
40°	25955
45°	16048
50°	11052
55°	7397
60°	5723
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P265054

CATALOG NUMBER: LD2B20D010 EU2B2010SP159035 2LBSQLC*MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	670.9	46.7
10°-20°	529.4	36.8
20°-30°	156.1	10.9
30°-40°	52.0	3.6
40°-50°	19.5	1.4
50°-60°	8.6	0.6
60°-70°	1.4	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1356.4	94.3
0°-40°	1408.4	97.9
0°-60°	1436.6	99.9
0°-90°	1438.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1438.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	10290	
5°	8343	671
15°	1742	529
25°	314	156
35°	78	52
45°	23	20
55°	9	9
65°	0	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P265054

CATALOG NUMBER: LD2B20D010 EU2B2010SP159035 2LBSQLC*MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	10289.5
2.5°	9874.8
5°	8342.7
7.5°	6427.7
10°	4455.0
12.5°	2851.0
15°	1742.3
17.5°	1062.6
20°	679.6
22.5°	455.0
25°	313.9
27.5°	221.7
30°	155.5
32.5°	109.4
35°	77.8
37.5°	54.7
40°	40.3
42.5°	31.7
45°	23.0
47.5°	20.2
50°	14.4
52.5°	11.5
55°	8.6
57.5°	8.6
60°	5.8
62.5°	2.9
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)