

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P224746

Luminaire Tested: **LD2B20D010 EU2B20FL409035 2LBD*MW**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P224746
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P14835)
Test Lab: INNOVATION CENTER (G1)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD2B20D010 EU2B20FL409035 2LBD*MW
Description: 2000 Lumen, 2inch Portfolio LED Downlight
FLOOD OPTIC
SPUN ROUND TRIM WITH MATTE WHITE FINISH
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1550.5 lumens
Efficiency: N/A
Efficacy: 74.2 lumens/watt
Spacing Criteria (0/90/45): 0.61 / 0.61 / 0.59
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 20.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P224746

CATALOG NUMBER: LD2B20D010 EU2B20FL409035 2LBD*MW

Luminous Intensity Polar Plot





TEST NUMBER: P224746

CATALOG NUMBER: LD2B20D010 EU2B20FL409035 2LBD*MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0			
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	99	98	97	95			
2	110	106	102	99	108	104	101	98	101	98	96	98	96	94	95	94	92	91			
3	105	100	96	93	104	99	95	92	96	93	90	94	91	89	92	90	88	86			
4	101	95	90	87	100	94	90	86	92	88	85	90	87	85	88	86	84	82			
5	98	91	86	82	96	90	85	82	88	84	81	86	83	80	85	82	80	79			
6	94	86	82	78	93	86	81	78	84	80	77	83	79	77	82	79	76	75			
7	90	83	78	74	89	82	77	74	81	77	74	80	76	73	79	76	73	72			
8	87	79	74	71	86	79	74	71	78	74	71	77	73	70	76	73	70	69			
9	84	76	71	68	83	76	71	68	75	71	68	74	70	67	73	70	67	66			
10	81	73	68	65	80	73	68	65	72	68	65	71	68	65	71	67	65	64			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1403703
5°	1378115
10°	1225078
15°	963467
20°	641144
25°	368067
30°	185930
35°	87479
40°	35193
45°	17420
50°	9581
55°	6686
60°	6198
65°	3666
70°	4530
75°	2993
80°	4461
85°	0



TEST NUMBER: P224746

CATALOG NUMBER: LD2B20D010 EU2B20FL409035 2LBD*MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	324.6	20.9
10°-20°	650.8	42.0
20°-30°	404.9	26.1
30°-40°	124.5	8.0
40°-50°	27.3	1.8
50°-60°	9.7	0.6
60°-70°	4.9	0.3
70°-80°	2.9	0.2
80°-90°	0.8	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1380.3	89.0
0°-40°	1504.8	97.1
0°-60°	1541.9	99.4
0°-90°	1550.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1550.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3624	
5°	3544	325
15°	2403	651
25°	861	405
35°	185	124
45°	32	27
55°	10	10
65°	4	5
75°	2	3
85°	0	1
90°	0	



TEST NUMBER: P224746

CATALOG NUMBER: LD2B20D010 EU2B20FL409035 2LBD*MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	3623.9
2.5°	3607.9
5°	3544.3
7.5°	3383.2
10°	3114.7
12.5°	2792.5
15°	2402.6
17.5°	1977.0
20°	1555.4
22.5°	1179.4
25°	861.2
27.5°	606.6
30°	415.7
32.5°	280.4
35°	185.0
37.5°	111.4
40°	69.6
42.5°	47.7
45°	31.8
47.5°	21.9
50°	15.9
52.5°	13.9
55°	9.9
57.5°	8.0
60°	8.0
62.5°	6.0
65°	4.0
67.5°	4.0
70°	4.0
72.5°	4.0
75°	2.0
77.5°	2.0
80°	2.0
82.5°	2.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)