

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P225119

Luminaire Tested: **LSSQWM2B05FL408050D010 2LBD*GPH**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P225119
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P14831)
Test Lab: INNOVATION CENTER (G1)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSSQWM2B05FL408050D010 2LBD*GPH
Description: 500 Lumen, 2inch Portfolio LED Cylinder
FLOOD OPTIC
SPUN ROUND TRIM WITH GRAPHITE FINISH
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 811.0 lumens
Efficiency: N/A
Efficacy: 111.1 lumens/watt
Spacing Criteria (0/90/45): 0.61 / 0.61 / 0.59
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 7.3
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P225119

CATALOG NUMBER: LSSQWM2B05FL408050D010 2LBD*GPH

Luminous Intensity Polar Plot





TEST NUMBER: P225119

CATALOG NUMBER: LSSQWM2B05FL408050D010 2LBD*GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10		50	30	10			50	30	10			0
RCR																				
0	119	119	119	119	116	116	116	116		111	111	111			106	106	106			100
1	114	112	110	108	112	110	108	106		106	104	103			102	101	100			95
2	110	106	102	100	108	104	101	98		101	99	96			98	96	94			91
3	106	100	96	93	104	99	95	92		96	93	91			94	92	89			87
4	102	95	91	87	100	94	90	87		92	89	86			90	87	85			83
5	98	91	86	83	96	90	85	82		88	84	81			87	83	81			79
6	94	87	82	78	93	86	81	78		85	81	78			83	80	77			75
7	91	83	78	75	89	82	78	74		81	77	74			80	76	74			72
8	87	80	75	71	86	79	74	71		78	74	71			77	73	71			69
9	84	76	72	68	83	76	71	68		75	71	68			74	70	68			66
10	81	73	69	65	80	73	68	65		72	68	65			72	68	65			64

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	735725
5°	720844
10°	640524
15°	502506
20°	337967
25°	196642
30°	98489
35°	45962
40°	21439
45°	9039
50°	4339
55°	2769
60°	1627
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P225119

CATALOG NUMBER: LSSQWM2B05FL408050D010 2LBD*GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	169.7	20.9
10°-20°	340.2	41.9
20°-30°	215.1	26.5
30°-40°	66.9	8.3
40°-50°	14.9	1.8
50°-60°	3.8	0.5
60°-70°	0.5	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	724.9	89.4
0°-40°	791.8	97.6
0°-60°	810.5	99.9
0°-90°	811.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	811.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1899	
5°	1854	170
15°	1253	340
25°	460	215
35°	97	67
45°	16	15
55°	4	4
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P225119

CATALOG NUMBER: LSSQWM2B05FL408050D010 2LBD*GPH

CANDELA DISTRIBUTION (FULL):

	0°
0°	1899.4
2.5°	1891.1
5°	1853.9
7.5°	1766.0
10°	1628.5
12.5°	1454.8
15°	1253.1
17.5°	1035.0
20°	819.9
22.5°	626.6
25°	460.1
27.5°	322.6
30°	220.2
32.5°	145.8
35°	97.2
37.5°	65.1
40°	42.4
42.5°	25.8
45°	16.5
47.5°	11.4
50°	7.2
52.5°	5.2
55°	4.1
57.5°	3.1
60°	2.1
62.5°	1.0
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)