

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P225340

Luminaire Tested: **LSSQWM2B05FL408050D010 2LBDC*MW**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P225340
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P14835)
Test Lab: INNOVATION CENTER (G1)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSSQWM2B05FL408050D010 2LBDC*MW
Description: 500 Lumen, 2inch Portfolio LED Cylinder
FLOOD OPTIC
CAST ROUND TRIM WITH MATTE WHITE FINISH
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 700.0 lumens
Efficiency: N/A
Efficacy: 95.9 lumens/watt
Spacing Criteria (0/90/45): 0.61 / 0.61 / 0.59
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 7.3
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P225340

CATALOG NUMBER: LSSQWM2B05FL408050D010 2LBDC*MW

Luminous Intensity Polar Plot





TEST NUMBER: P225340

CATALOG NUMBER: LSSQWM2B05FL408050D010 2LBDC*MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					0
RW	70	50	30	10		70	50	30	10		50	30	10			50	30	10			0
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111			106	106	106			100
1	114	112	110	108		112	110	108	106		106	104	103			102	101	100			95
2	110	106	102	99		108	104	101	98		101	98	96			98	96	94			91
3	105	100	96	93		104	99	95	92		96	93	90			94	91	89			86
4	101	95	90	87		100	94	90	86		92	88	85			90	87	85			82
5	98	91	86	82		96	90	85	82		88	84	81			86	83	80			79
6	94	86	82	78		93	86	81	78		84	80	77			83	79	77			75
7	90	83	78	74		89	82	77	74		81	77	74			80	76	73			72
8	87	79	74	71		86	79	74	71		78	74	71			77	73	70			69
9	84	76	71	68		83	76	71	68		75	71	68			74	70	67			66
10	81	73	68	65		80	73	68	65		72	68	65			71	68	65			64

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	633737
5°	622160
10°	553089
15°	434976
20°	289450
25°	166169
30°	83952
35°	39484
40°	15877
45°	7888
50°	4339
55°	3039
60°	2789
65°	1650
70°	2039
75°	1347
80°	2008
85°	0



TEST NUMBER: P225340

CATALOG NUMBER: LSSQWM2B05FL408050D010 2LBDC*MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	146.5	20.9
10°-20°	293.8	42.0
20°-30°	182.8	26.1
30°-40°	56.2	8.0
40°-50°	12.4	1.8
50°-60°	4.4	0.6
60°-70°	2.2	0.3
70°-80°	1.3	0.2
80°-90°	0.4	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	623.2	89.0
0°-40°	679.4	97.0
0°-60°	696.2	99.4
0°-90°	700.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	700.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1636	
5°	1600	147
15°	1085	294
25°	389	183
35°	84	56
45°	14	12
55°	4	4
65°	2	2
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P225340

CATALOG NUMBER: LSSQWM2B05FL408050D010 2LBDC*MW

CANDELA DISTRIBUTION (FULL):

0°	
0°	1636.1
2.5°	1628.9
5°	1600.1
7.5°	1527.4
10°	1406.2
12.5°	1260.7
15°	1084.7
17.5°	892.6
20°	702.2
22.5°	532.5
25°	388.8
27.5°	273.9
30°	187.7
32.5°	126.6
35°	83.5
37.5°	50.3
40°	31.4
42.5°	21.6
45°	14.4
47.5°	9.9
50°	7.2
52.5°	6.3
55°	4.5
57.5°	3.6
60°	3.6
62.5°	2.7
65°	1.8
67.5°	1.8
70°	1.8
72.5°	1.8
75°	0.9
77.5°	0.9
80°	0.9
82.5°	0.9
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)