

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P224009

Luminaire Tested: **LSSQWM2B05SP158050D010 2LBDL*WMH**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P224009
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (150)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSSQWM2B05SP158050D010 2LBDL*WMH
Description: 500 Lumen, 2inch Portfolio LED Cylinder
SPOT OPTIC
LENSED SPUN ROUND TRIM WITH WHEAT METALLIC HAZE FINISH
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 426.0 lumens
Efficiency: N/A
Efficacy: 58.4 lumens/watt
Spacing Criteria (0/90/45): 0.24 / 0.24 / 0.23
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 7.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P224009

CATALOG NUMBER: LSSQWM2B05SP158050D010 2LBDL*WMH

Luminous Intensity Polar Plot





TEST NUMBER: P224009

CATALOG NUMBER: LSSQWM2B05SP158050D010 2LBDL*WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10		50	30	10			50	30	10			0
RCR																				
0	119	119	119	119	116	116	116	116		111	111	111			106	106	106			102
1	116	114	112	111	113	112	110	109		108	107	106			104	103	103			101
2	113	110	107	105	111	108	106	104		105	103	102			102	101	100			100
3	110	106	103	101	108	105	102	100		102	100	98			100	99	97			98
4	108	103	100	97	106	102	99	97		100	98	96			98	96	95			97
5	105	101	97	95	104	100	97	94		98	96	94			97	95	93			96
6	103	98	95	93	102	98	95	92		96	94	92			95	93	91			94
7	101	96	93	91	100	96	93	90		95	92	90			94	91	90			93
8	100	94	91	89	99	94	91	89		93	90	89			92	90	88			92
9	98	93	90	88	97	92	89	87		92	89	87			91	89	87			90
10	96	91	88	86	96	91	88	86		90	88	86			90	87	86			89

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	2047007
5°	1479792
10°	430805
15°	151181
20°	64716
25°	29105
30°	11271
35°	5580
40°	3742
45°	2410
50°	1326
55°	1013
60°	542
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P224009

CATALOG NUMBER: LSSQWM2B05SP158050D010 2LBDL*WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	269.3	63.2
10°-20°	109.6	25.7
20°-30°	33.6	7.9
30°-40°	8.3	1.9
40°-50°	3.4	0.8
50°-60°	1.5	0.3
60°-70°	0.3	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	412.5	96.8
0°-40°	420.8	98.8
0°-60°	425.7	99.9
0°-90°	426.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	426.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	5285	
5°	3806	269
15°	377	110
25°	68	34
35°	12	8
45°	4	3
55°	2	1
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P224009

CATALOG NUMBER: LSSQWM2B05SP158050D010 2LBDL*WMH

CANDELA DISTRIBUTION (FULL):

	0°
0°	5284.7
1°	5204.0
2°	5007.0
3°	4693.0
4°	4282.7
5°	3805.8
6°	3268.1
7°	2684.6
8°	2092.9
9°	1539.7
10°	1095.3
11°	785.0
12°	590.2
13°	480.6
14°	420.6
15°	377.0
17.5°	232.5
20°	157.0
22.5°	105.2
25°	68.1
27.5°	41.5
30°	25.2
32.5°	16.3
35°	11.8
37.5°	9.6
40°	7.4
42.5°	5.9
45°	4.4
47.5°	3.0
50°	2.2
52.5°	2.2
55°	1.5
57.5°	1.5
60°	0.7
62.5°	0.7
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0



TEST NUMBER: P224009

CATALOG NUMBER: LSSQWM2B05SP158050D010 2LBDL*WMH

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







85°	0.0
87.5°	0.0



(END OF REPORT)