

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P225314

Luminaire Tested: **LD2B20D010 EU2B20FL408040 2LBDC*MMS**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P225314
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P14835)
Test Lab: INNOVATION CENTER (G1)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD2B20D010 EU2B20FL408040 2LBDC*MMS
Description: 2000 Lumen, 2inch Portfolio LED Downlight
FLOOD OPTIC
CAST ROUND TRIM WITH MATTE METALLIC SILVER
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1964.7 lumens
Efficiency: N/A
Efficacy: 94.0 lumens/watt
Spacing Criteria (0/90/45): 0.61 / 0.61 / 0.59
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 20.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P225314

CATALOG NUMBER: LD2B20D010 EU2B20FL408040 2LBDC*MMS

Luminous Intensity Polar Plot





TEST NUMBER: P225314

CATALOG NUMBER: LD2B20D010 EU2B20FL408040 2LBDC*MMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10			50	30	10			0
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111			106	106	106			100
1	114	112	110	108		112	110	108	106		106	104	103			102	101	100			95
2	110	106	102	99		108	104	101	98		101	98	96			98	96	94			91
3	105	100	96	93		104	99	95	92		96	93	90			94	91	89			86
4	101	95	90	87		100	94	90	86		92	88	85			90	87	85			82
5	98	91	86	82		96	90	85	82		88	84	81			86	83	80			79
6	94	87	82	78		93	86	81	78		84	80	77			83	80	77			75
7	90	83	78	74		89	82	77	74		81	77	74			80	76	73			72
8	87	79	74	71		86	79	74	71		78	74	71			77	73	70			69
9	84	76	71	68		83	76	71	68		75	71	68			74	70	67			66
10	81	73	68	65		80	73	68	65		72	68	65			71	68	65			64

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1778770
5°	1746332
10°	1552400
15°	1220915
20°	812415
25°	466410
30°	235621
35°	110839
40°	44598
45°	22076
50°	12173
55°	8509
60°	7824
65°	4583
70°	5663
75°	3741
80°	5577
85°	0



TEST NUMBER: P225314

CATALOG NUMBER: LD2B20D010 EU2B20FL408040 2LBDC*MMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	411.3	20.9
10°-20°	824.7	42.0
20°-30°	513.1	26.1
30°-40°	157.8	8.0
40°-50°	34.7	1.8
50°-60°	12.3	0.6
60°-70°	6.2	0.3
70°-80°	3.6	0.2
80°-90°	1.0	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1749.1	89.0
0°-40°	1906.9	97.1
0°-60°	1953.9	99.4
0°-90°	1964.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1964.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4592	
5°	4491	411
15°	3045	825
25°	1091	513
35°	234	158
45°	40	35
55°	13	12
65°	5	6
75°	2	4
85°	0	1
90°	0	



TEST NUMBER: P225314

CATALOG NUMBER: LD2B20D010 EU2B20FL408040 2LBDC*MMS

CANDELA DISTRIBUTION (FULL):

0°	
0°	4592.2
2.5°	4572.0
5°	4491.3
7.5°	4287.2
10°	3946.9
12.5°	3538.6
15°	3044.6
17.5°	2505.3
20°	1970.9
22.5°	1494.6
25°	1091.3
27.5°	768.7
30°	526.8
32.5°	355.4
35°	234.4
37.5°	141.1
40°	88.2
42.5°	60.5
45°	40.3
47.5°	27.7
50°	20.2
52.5°	17.6
55°	12.6
57.5°	10.1
60°	10.1
62.5°	7.6
65°	5.0
67.5°	5.0
70°	5.0
72.5°	5.0
75°	2.5
77.5°	2.5
80°	2.5
82.5°	2.5
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)