

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P264667

Luminaire Tested: **LD2B15D010 EU2B1510SP158030 2LBDL*H**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P264667
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1711-432-2)
Test Lab: INNOVATION CENTER(G3)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD2B15D010 EU2B1510SP158030 2LBDL*H
Description: 1500 Lumen, 2inch Portfolio LED Downlight
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1238.0 lumens
Efficiency: N/A
Efficacy: 86.6 lumens/watt
Spacing Criteria (0/90/45): 0.31 / 0.31 / 0.32
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 14.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P264667

CATALOG NUMBER: LD2B15D010 EU2B1510SP158030 2LBDL*H

Luminous Intensity Polar Plot





TEST NUMBER: P264667

CATALOG NUMBER: LD2B15D010 EU2B1510SP158030 2LBDL*H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10			50	30	10			0
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111			106	106	106			100
1	115	113	111	110		113	111	110	108		107	106	105			104	103	102			97
2	112	108	106	103		110	107	104	102		104	102	100			101	99	98			94
3	109	104	101	98		107	103	100	97		100	98	96			98	96	94			92
4	105	100	97	94		104	99	96	93		97	95	92			96	93	91			89
5	103	97	93	91		101	96	93	90		95	92	89			93	91	89			87
6	100	94	90	88		99	94	90	87		92	89	87			91	88	86			85
7	98	92	88	85		97	91	88	85		90	87	85			89	86	84			83
8	95	89	86	83		94	89	85	83		88	85	82			87	84	82			81
9	93	87	83	81		92	87	83	81		86	83	81			85	82	80			79
10	91	85	82	79		91	85	81	79		84	81	79			84	81	79			78

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	4370396
5°	3557057
10°	1921431
15°	766149
20°	307192
25°	147087
30°	76281
35°	40293
40°	22348
45°	13815
50°	9517
55°	6365
60°	4934
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P264667

CATALOG NUMBER: LD2B15D010 EU2B1510SP158030 2LBDL*H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	577.6	46.7
10°-20°	455.7	36.8
20°-30°	134.4	10.9
30°-40°	44.7	3.6
40°-50°	16.8	1.4
50°-60°	7.4	0.6
60°-70°	1.2	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1167.8	94.3
0°-40°	1212.5	97.9
0°-60°	1236.8	99.9
0°-90°	1238.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1238.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	8858	
5°	7182	578
15°	1500	456
25°	270	134
35°	67	45
45°	20	17
55°	7	7
65°	0	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P264667

CATALOG NUMBER: LD2B15D010 EU2B1510SP158030 2LBDL*H

CANDELA DISTRIBUTION (FULL):

0°	
0°	8858.4
2.5°	8501.4
5°	7182.4
7.5°	5533.7
10°	3835.4
12.5°	2454.5
15°	1500.0
17.5°	914.8
20°	585.1
22.5°	391.7
25°	270.2
27.5°	190.9
30°	133.9
32.5°	94.2
35°	66.9
37.5°	47.1
40°	34.7
42.5°	27.3
45°	19.8
47.5°	17.4
50°	12.4
52.5°	9.9
55°	7.4
57.5°	7.4
60°	5.0
62.5°	2.5
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)