

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P264312

Luminaire Tested: **LD2B15D010 EU2B1510SP159030 2LBSQC*MB**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P264312
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1805-787-1)
Test Lab: INNOVATION CENTER(G2)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD2B15D010 EU2B1510SP159030 2LBSQC*MB
Description: 1500 Lumen, 2inch Portfolio LED Downlight
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1033.1 lumens
Efficiency: N/A
Efficacy: 72.2 lumens/watt
Spacing Criteria (0/90/45): 0.28 / 0.28 / 0.28
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 14.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P264312

CATALOG NUMBER: LD2B15D010 EU2B1510SP159030 2LBSQC*MB

Luminous Intensity Polar Plot





TEST NUMBER: P264312

CATALOG NUMBER: LD2B15D010 EU2B1510SP159030 2LBSQC*MB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10			50	30	10			0
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111			106	106	106			100
1	116	114	112	111		113	112	110	109		108	107	106			104	103	102			98
2	113	109	107	105		111	108	106	104		105	103	101			102	101	99			96
3	110	106	103	100		108	105	102	100		102	100	98			100	98	97			94
4	107	103	99	97		106	102	99	96		100	97	95			98	96	94			92
5	105	100	97	94		104	99	96	94		98	95	93			96	94	92			90
6	103	98	94	92		102	97	94	91		96	93	91			95	92	90			89
7	101	95	92	90		100	95	92	89		94	91	89			93	90	89			87
8	99	93	90	88		98	93	90	88		92	89	87			91	89	87			86
9	97	92	88	86		96	91	88	86		91	88	86			90	87	86			85
10	95	90	87	85		95	90	87	85		89	86	85			89	86	84			83

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	4874316
5°	3906998
10°	1705261
15°	528438
20°	184231
25°	81382
30°	36859
35°	19153
40°	10949
45°	5163
50°	3224
55°	1806
60°	1085
65°	1284
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P264312

CATALOG NUMBER: LD2B15D010 EU2B1510SP159030 2LBSQC*MB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	599.1	58.0
10°-20°	328.1	31.8
20°-30°	74.8	7.2
30°-40°	21.5	2.1
40°-50°	6.6	0.6
50°-60°	2.0	0.2
60°-70°	1.0	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1002.0	97.0
0°-40°	1023.5	99.1
0°-60°	1032.1	99.9
0°-90°	1033.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1033.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	9880	
5°	7889	599
15°	1035	328
25°	150	75
35°	32	21
45°	7	7
55°	2	2
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P264312

CATALOG NUMBER: LD2B15D010 EU2B1510SP159030 2LBSQC*MB

CANDELA DISTRIBUTION (FULL):

	0°
0°	9879.8
1°	9756.8
2°	9501.4
3°	9104.9
4°	8560.0
5°	7889.0
6°	7066.4
7°	6147.3
8°	5188.0
9°	4259.3
10°	3403.9
11°	2679.8
12°	2109.5
13°	1660.1
14°	1311.3
15°	1034.6
16°	816.3
17°	649.8
18°	522.6
19°	425.1
20°	350.9
22.5°	226.9
25°	149.5
26°	126.1
27°	107.1
28°	90.1
29°	75.3
30°	64.7
32.5°	44.5
35°	31.8
37.5°	23.3
40°	17.0
42.5°	11.7
45°	7.4
47.5°	5.3
50°	4.2
52.5°	3.2
55°	2.1
57.5°	1.1
60°	1.1
62.5°	1.1
65°	1.1
67.5°	1.1



TEST NUMBER: P264312

CATALOG NUMBER: LD2B15D010 EU2B1510SP159030 2LBSQC*MB

CANDELA DISTRIBUTION (continued):

	0°
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







70°	0.0
72.5°	0.0



(END OF REPORT)