

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P#

Luminaire Tested: **LD2B05D010 EU2B05FL409035 2LBD\*LI**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P#  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P29152)  
Test Lab: INNOVATION CENTER-P2  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LD2B05D010 EU2B05FL409035 2LBD\*LI  
Description: 500 Lumen, 2inch Portfolio LED Downlight  
FLOOD OPTIC  
SPUN ROUND TRIM WITH LI FINISH  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 646.0 lumens  
Efficiency: N/A  
Efficacy: 88.5 lumens/watt  
Spacing Criteria (0/90/45): 0.59 / 0.59 / 0.58  
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')  
CIE Type: Direct


Input Watts (W): 7.3  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P#

CATALOG NUMBER: LD2B05D010 EU2B05FL409035 2LBD\*LI

### Luminous Intensity Polar Plot



0% Up  
100% Dn



TEST NUMBER: P#

CATALOG NUMBER: LD2B05D010 EU2B05FL409035 2LBD\*LI

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10		0		
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	114	112	110	108	112	110	108	106	106	105	103	102	101	100	99	98	97	96			
2	110	106	103	100	108	104	101	99	101	99	97	98	96	95	96	94	93	91			
3	106	101	96	93	104	99	95	92	97	94	91	94	92	90	92	90	88	87			
4	102	96	91	88	100	95	90	87	93	89	86	91	88	85	89	86	84	83			
5	98	91	86	83	97	90	86	83	89	85	82	87	84	81	86	83	81	79			
6	94	87	82	79	93	86	82	79	85	81	78	84	80	78	83	79	77	76			
7	91	83	79	75	90	83	78	75	82	78	75	81	77	74	80	76	74	73			
8	88	80	75	72	87	80	75	72	79	74	71	78	74	71	77	73	71	70			
9	85	77	72	69	84	76	72	69	76	71	69	75	71	68	74	71	68	67			
10	82	74	69	66	81	74	69	66	73	69	66	72	68	66	72	68	66	65			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	619676
5°	595486
10°	518398
15°	404780
20°	269211
25°	154159
30°	76617
35°	35228
40°	14107
45°	6464
50°	3013
55°	1688
60°	930
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P#

CATALOG NUMBER: LD2B05D010 EU2B05FL409035 2LBD\*LI

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	139.4	21.6
10°-20°	273.7	42.4
20°-30°	169.4	26.2
30°-40°	50.7	7.8
40°-50°	10.2	1.6
50°-60°	2.5	0.4
60°-70°	0.1	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	582.5	90.2
0°-40°	633.2	98.0
0°-60°	645.9	100.0
0°-90°	646.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	646.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1600	
5°	1532	139
15°	1009	274
25°	361	169
35°	74	51
45°	12	10
55°	2	2
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P#

CATALOG NUMBER: LD2B05D010 EU2B05FL409035 2LBD\*LI

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	1599.8
1°	1591.1
2°	1583.1
3°	1566.9
4°	1552.0
5°	1531.5
6°	1503.6
7°	1468.2
8°	1422.9
9°	1371.4
10°	1318.0
11°	1262.7
12°	1203.7
13°	1142.3
14°	1076.5
15°	1009.4
17.5°	832.5
20°	653.1
22.5°	494.2
25°	360.7
27.5°	253.3
30°	171.3
32.5°	113.0
35°	74.5
37.5°	46.6
40°	27.9
42.5°	18.0
45°	11.8
47.5°	7.4
50°	5.0
52.5°	3.7
55°	2.5
57.5°	1.9
60°	1.2
62.5°	0.0
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0



TEST NUMBER: P#

CATALOG NUMBER: LD2B05D010 EU2B05FL409035 2LBD\*LI

CANDELA DISTRIBUTION (continued):

0°  
90° | 0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







85°		0.0
87.5°		0.0



(END OF REPORT)