

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P264156

Luminaire Tested: **LD2B15D010 EU2B1510SP158050 2LBSQC*MB**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P264156
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1805-787-1)
Test Lab: INNOVATION CENTER(G2)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD2B15D010 EU2B1510SP158050 2LBSQC*MB
Description: 1500 Lumen, 2inch Portfolio LED Downlight
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1340.1 lumens
Efficiency: N/A
Efficacy: 93.7 lumens/watt
Spacing Criteria (0/90/45): 0.28 / 0.28 / 0.28
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 14.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P264156

CATALOG NUMBER: LD2B15D010 EU2B1510SP158050 2LBSQC*MB

Luminous Intensity Polar Plot





TEST NUMBER: P264156

CATALOG NUMBER: LD2B15D010 EU2B1510SP158050 2LBSQC*MB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	116	114	112	111	113	112	110	109	108	107	106		104	103	102		101
2	113	109	107	105	111	108	106	104	105	103	101		102	101	99		99
3	110	106	103	100	108	105	102	100	102	100	98		100	98	97		98
4	107	103	99	97	106	102	99	96	100	97	95		98	96	94		96
5	105	100	97	94	104	99	96	94	98	95	93		96	94	92		95
6	103	98	94	92	102	97	94	91	96	93	91		95	92	90		93
7	101	95	92	90	100	95	92	89	94	91	89		93	90	89		92
8	99	93	90	88	98	93	90	88	92	89	87		91	89	87		91
9	97	92	88	86	96	91	88	86	91	88	86		90	87	86		89
10	95	90	87	85	95	90	87	85	89	86	85		89	86	84		88

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	6322925
5°	5068153
10°	2212045
15°	685499
20°	238991
25°	105552
30°	47797
35°	24874
40°	14169
45°	6698
50°	4221
55°	2408
60°	1381
65°	1634
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P264156

CATALOG NUMBER: LD2B15D010 EU2B1510SP158050 2LBSQC*MB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	777.1	58.0
10°-20°	425.6	31.8
20°-30°	97.0	7.2
30°-40°	27.9	2.1
40°-50°	8.6	0.6
50°-60°	2.6	0.2
60°-70°	1.2	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1299.7	97.0
0°-40°	1327.6	99.1
0°-60°	1338.8	99.9
0°-90°	1340.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1340.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	12816	
5°	10234	777
15°	1342	426
25°	194	97
35°	41	28
45°	10	9
55°	3	3
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P264156

CATALOG NUMBER: LD2B15D010 EU2B1510SP158050 2LBSQC*MB

CANDELA DISTRIBUTION (FULL):

	0°
0°	12816.0
1°	12656.5
2°	12325.1
3°	11810.8
4°	11104.0
5°	10233.6
6°	9166.5
7°	7974.3
8°	6729.8
9°	5525.2
10°	4415.5
11°	3476.3
12°	2736.5
13°	2153.4
14°	1701.0
15°	1342.1
16°	1058.8
17°	842.9
18°	677.9
19°	551.4
20°	455.2
22.5°	294.3
25°	193.9
26°	163.6
27°	138.9
28°	116.9
29°	97.6
30°	83.9
32.5°	57.8
35°	41.3
37.5°	30.3
40°	22.0
42.5°	15.1
45°	9.6
47.5°	6.9
50°	5.5
52.5°	4.1
55°	2.8
57.5°	1.4
60°	1.4
62.5°	1.4
65°	1.4
67.5°	1.4



TEST NUMBER: P264156

CATALOG NUMBER: LD2B15D010 EU2B1510SP158050 2LBSQC*MB

CANDELA DISTRIBUTION (continued):

	0°
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







70°	0.0
72.5°	0.0



(END OF REPORT)