

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P264158

Luminaire Tested: **LD2B15D010 EU2B1510SP158050 2LBSQC*MMS**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P264158
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1805-787-1)
Test Lab: INNOVATION CENTER(G2)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD2B15D010 EU2B1510SP158050 2LBSQC*MMS
Description: 1500 Lumen, 2inch Portfolio LED Downlight
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1413.1 lumens
Efficiency: N/A
Efficacy: 98.8 lumens/watt
Spacing Criteria (0/90/45): 0.28 / 0.28 / 0.28
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 14.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P264158

CATALOG NUMBER: LD2B15D010 EU2B1510SP158050 2LBSQC*MMS

Luminous Intensity Polar Plot





TEST NUMBER: P264158

CATALOG NUMBER: LD2B15D010 EU2B1510SP158050 2LBSQC*MMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	116	114	112	111	113	112	110	109	108	107	106		104	103	102		101
2	113	109	107	105	111	108	106	104	105	103	101		102	101	99		99
3	110	106	103	100	108	105	102	100	102	100	98		100	98	97		98
4	107	103	99	97	106	102	99	96	100	97	95		98	96	94		96
5	105	100	97	94	104	99	96	94	98	95	93		96	94	92		95
6	103	98	94	92	102	97	94	91	96	93	91		95	92	90		93
7	101	95	92	90	100	95	92	89	94	91	89		93	90	89		92
8	99	93	90	88	98	93	90	88	92	89	87		91	89	87		91
9	97	92	88	86	96	91	88	86	91	88	86		90	87	86		89
10	95	90	87	85	95	90	87	85	89	86	84		89	86	84		88

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	6667390
5°	5344253
10°	2332529
15°	722836
20°	252012
25°	111323
30°	50417
35°	26199
40°	14942
45°	7117
50°	4452
55°	2494
60°	1480
65°	1751
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P264158

CATALOG NUMBER: LD2B15D010 EU2B1510SP158050 2LBSQC*MMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	819.5	58.0
10°-20°	448.8	31.8
20°-30°	102.3	7.2
30°-40°	29.4	2.1
40°-50°	9.1	0.6
50°-60°	2.8	0.2
60°-70°	1.3	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1370.6	97.0
0°-40°	1400.0	99.1
0°-60°	1411.8	99.9
0°-90°	1413.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1413.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	13514	
5°	10791	819
15°	1415	449
25°	204	102
35°	44	29
45°	10	9
55°	3	3
65°	2	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P264158

CATALOG NUMBER: LD2B15D010 EU2B1510SP158050 2LBSQC*MMS

CANDELA DISTRIBUTION (FULL):

	0°
0°	13514.2
1°	13346.0
2°	12996.6
3°	12454.2
4°	11708.9
5°	10791.1
6°	9665.9
7°	8408.7
8°	7096.4
9°	5826.2
10°	4656.0
11°	3665.7
12°	2885.5
13°	2270.7
14°	1793.7
15°	1415.2
16°	1116.5
17°	888.9
18°	714.9
19°	581.5
20°	480.0
22.5°	310.3
25°	204.5
26°	172.6
27°	146.5
28°	123.3
29°	103.0
30°	88.5
32.5°	60.9
35°	43.5
37.5°	31.9
40°	23.2
42.5°	16.0
45°	10.2
47.5°	7.3
50°	5.8
52.5°	4.4
55°	2.9
57.5°	1.5
60°	1.5
62.5°	1.5
65°	1.5
67.5°	1.5



TEST NUMBER: P264158

CATALOG NUMBER: LD2B15D010 EU2B1510SP158050 2LBSQC*MMS

CANDELA DISTRIBUTION (continued):

	0°
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







70°	0.0
72.5°	0.0



(END OF REPORT)