

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P264157

Luminaire Tested: **LD2B15D010 EU2B1510SP158050 2LBSQC*MW**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P264157
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1805-787-1)
Test Lab: INNOVATION CENTER(G2)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD2B15D010 EU2B1510SP158050 2LBSQC*MW
Description: 1500 Lumen, 2inch Portfolio LED Downlight
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1228.0 lumens
Efficiency: N/A
Efficacy: 85.9 lumens/watt
Spacing Criteria (0/90/45): 0.28 / 0.28 / 0.28
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 14.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P264157

CATALOG NUMBER: LD2B15D010 EU2B1510SP158050 2LBSQC*MW

Luminous Intensity Polar Plot





TEST NUMBER: P264157

CATALOG NUMBER: LD2B15D010 EU2B1510SP158050 2LBSQC*MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	116	114	112	111	113	112	110	109	108	107	106		104	103	102		101
2	113	109	107	105	111	108	106	104	105	103	101		102	101	99		99
3	110	106	103	100	108	105	102	100	102	100	98		100	98	97		98
4	107	103	99	97	106	102	99	96	100	97	95		98	96	94		96
5	105	100	97	94	104	99	96	94	98	95	93		96	94	92		95
6	103	98	94	92	102	97	94	91	96	93	91		95	92	90		93
7	101	95	92	90	100	95	92	89	94	91	89		93	90	89		92
8	99	93	90	88	98	93	90	88	92	89	87		91	89	87		91
9	97	92	88	86	96	91	88	86	91	88	86		90	87	86		89
10	95	90	87	85	95	90	87	85	89	86	85		89	86	84		88

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	5794436
5°	4644519
10°	2027136
15°	628191
20°	218988
25°	96734
30°	43809
35°	22766
40°	13010
45°	6140
50°	3838
55°	2150
60°	1283
65°	1518
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P264157

CATALOG NUMBER: LD2B15D010 EU2B1510SP158050 2LBSQC*MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	712.2	58.0
10°-20°	390.0	31.8
20°-30°	88.9	7.2
30°-40°	25.6	2.1
40°-50°	7.9	0.6
50°-60°	2.4	0.2
60°-70°	1.1	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1191.1	97.0
0°-40°	1216.7	99.1
0°-60°	1226.9	99.9
0°-90°	1228.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1228.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	11745	
5°	9378	712
15°	1230	390
25°	178	89
35°	38	26
45°	9	8
55°	2	2
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P264157

CATALOG NUMBER: LD2B15D010 EU2B1510SP158050 2LBSQC*MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	11744.8
1°	11598.7
2°	11295.0
3°	10823.6
4°	10175.9
5°	9378.2
6°	8400.3
7°	7307.8
8°	6167.3
9°	5063.4
10°	4046.4
11°	3185.7
12°	2507.7
13°	1973.4
14°	1558.8
15°	1229.9
16°	970.3
17°	772.5
18°	621.3
19°	505.3
20°	417.1
22.5°	269.7
25°	177.7
26°	150.0
27°	127.3
28°	107.1
29°	89.5
30°	76.9
32.5°	52.9
35°	37.8
37.5°	27.7
40°	20.2
42.5°	13.9
45°	8.8
47.5°	6.3
50°	5.0
52.5°	3.8
55°	2.5
57.5°	1.3
60°	1.3
62.5°	1.3
65°	1.3
67.5°	1.3



TEST NUMBER: P264157

CATALOG NUMBER: LD2B15D010 EU2B1510SP158050 2LBSQC*MW

CANDELA DISTRIBUTION (continued):

	0°
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







70°	0.0
72.5°	0.0



(END OF REPORT)