

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P224579

Luminaire Tested: **LD2B15D010 EU2B15FL408050 2LBDL*GPH**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P224579
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P14831)
Test Lab: INNOVATION CENTER (G1)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD2B15D010 EU2B15FL408050 2LBDL*GPH
Description: 1500 Lumen, 2inch Portfolio LED Downlight
FLOOD OPTIC
LENSED SPUN ROUND TRIM WITH GRAPHITE FINISH
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1366.6 lumens
Efficiency: N/A
Efficacy: 95.6 lumens/watt
Spacing Criteria (0/90/45): 0.61 / 0.61 / 0.59
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 14.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P224579

CATALOG NUMBER: LD2B15D010 EU2B15FL408050 2LBDL*GPH

Luminous Intensity Polar Plot





TEST NUMBER: P224579

CATALOG NUMBER: LD2B15D010 EU2B15FL408050 2LBDL*GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10			50	30	10			0
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111			106	106	106			100
1	114	112	110	108		112	110	108	106		106	104	103			102	101	100			95
2	110	106	102	100		108	104	101	98		101	99	96			98	96	94			91
3	106	100	96	93		104	99	95	92		96	93	91			94	92	89			87
4	102	95	91	87		100	94	90	87		92	89	86			90	87	85			83
5	98	91	86	83		96	90	85	82		88	84	81			87	83	81			79
6	94	87	82	78		93	86	81	78		85	81	78			83	80	77			75
7	91	83	78	75		89	82	78	74		81	77	74			80	76	74			72
8	87	80	75	71		86	79	74	71		78	74	71			77	73	71			69
9	84	76	72	68		83	76	71	68		75	71	68			74	70	68			66
10	81	73	69	65		80	73	68	65		72	68	65			72	68	65			64

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1239740
5°	1214652
10°	1079313
15°	846773
20°	569502
25°	331355
30°	165981
35°	77455
40°	36103
45°	15283
50°	7352
55°	4727
60°	2711
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P224579

CATALOG NUMBER: LD2B15D010 EU2B15FL408050 2LBDL*GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	286.0	20.9
10°-20°	573.2	41.9
20°-30°	362.4	26.5
30°-40°	112.8	8.3
40°-50°	25.1	1.8
50°-60°	6.4	0.5
60°-70°	0.8	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1221.6	89.4
0°-40°	1334.3	97.6
0°-60°	1365.8	99.9
0°-90°	1366.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1366.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3201	
5°	3124	286
15°	2112	573
25°	775	362
35°	164	113
45°	28	25
55°	7	6
65°	0	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P224579

CATALOG NUMBER: LD2B15D010 EU2B15FL408050 2LBDL*GPH

CANDELA DISTRIBUTION (FULL):

	0°
0°	3200.6
2.5°	3186.6
5°	3123.9
7.5°	2975.8
10°	2744.1
12.5°	2451.4
15°	2111.6
17.5°	1744.0
20°	1381.6
22.5°	1055.8
25°	775.3
27.5°	543.6
30°	371.1
32.5°	245.7
35°	163.8
37.5°	109.8
40°	71.4
42.5°	43.6
45°	27.9
47.5°	19.2
50°	12.2
52.5°	8.7
55°	7.0
57.5°	5.2
60°	3.5
62.5°	1.7
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)