

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P224508

Luminaire Tested: **LD2B15D010 EU2B15FL408050 2LBDL*WMH**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P224508
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P14831)
Test Lab: INNOVATION CENTER (G1)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD2B15D010 EU2B15FL408050 2LBDL*WMH
Description: 1500 Lumen, 2inch Portfolio LED Downlight
FLOOD OPTIC
LENSED SPUN ROUND TRIM WITH WHEAT METALLIC HAZE FINISH
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1383.4 lumens
Efficiency: N/A
Efficacy: 96.7 lumens/watt
Spacing Criteria (0/90/45): 0.61 / 0.61 / 0.59
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 14.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P224508

CATALOG NUMBER: LD2B15D010 EU2B15FL408050 2LBDL*WMH

Luminous Intensity Polar Plot





TEST NUMBER: P224508

CATALOG NUMBER: LD2B15D010 EU2B15FL408050 2LBDL*WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	114	112	110	108		112	110	108	106		106	104	103		102	101	100		99	98	97
2	110	106	102	100		108	104	101	98		101	98	96		98	96	94		95	94	92
3	106	100	96	93		104	99	95	92		96	93	91		94	91	89		92	90	88
4	102	95	91	87		100	94	90	87		92	89	86		90	87	85		88	86	84
5	98	91	86	82		96	90	85	82		88	84	81		87	83	81		85	82	80
6	94	87	82	78		93	86	81	78		85	81	77		83	80	77		82	79	77
7	91	83	78	75		89	82	78	74		81	77	74		80	76	74		79	76	73
8	87	79	75	71		86	79	74	71		78	74	71		77	73	71		76	73	70
9	84	76	71	68		83	76	71	68		75	71	68		74	70	68		73	70	67
10	81	73	69	65		80	73	68	65		72	68	65		72	68	65		71	67	65

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1255350
5°	1229467
10°	1089186
15°	855876
20°	575438
25°	334304
30°	167055
35°	78779
40°	37266
45°	16324
50°	8436
55°	4727
60°	2711
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P224508

CATALOG NUMBER: LD2B15D010 EU2B15FL408050 2LBDL*WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	289.3	20.9
10°-20°	578.9	41.8
20°-30°	365.9	26.5
30°-40°	114.5	8.3
40°-50°	26.6	1.9
50°-60°	7.0	0.5
60°-70°	1.3	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1234.1	89.2
0°-40°	1348.6	97.5
0°-60°	1382.1	99.9
0°-90°	1383.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1383.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3241	
5°	3162	289
15°	2134	579
25°	782	366
35°	167	114
45°	30	27
55°	7	7
65°	0	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P224508

CATALOG NUMBER: LD2B15D010 EU2B15FL408050 2LBDL*WMH

CANDELA DISTRIBUTION (FULL):

	0°
0°	3240.9
2.5°	3225.2
5°	3162.0
7.5°	3013.0
10°	2769.2
12.5°	2479.8
15°	2134.3
17.5°	1757.3
20°	1396.0
22.5°	1062.8
25°	782.2
27.5°	552.4
30°	373.5
32.5°	249.0
35°	166.6
37.5°	112.2
40°	73.7
42.5°	45.6
45°	29.8
47.5°	21.0
50°	14.0
52.5°	10.5
55°	7.0
57.5°	5.3
60°	3.5
62.5°	3.5
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)