

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P223109

Luminaire Tested: **LD2B15D010 EU2B15NFL258050 2LBD*GPH**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P223109
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (155)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD2B15D010 EU2B15NFL258050 2LBD*GPH
Description: 1500 Lumen, 2inch Portfolio LED Downlight
NARROW FLOOD OPTIC
SPUN ROUND TRIM WITH GRAPHITE FINISH
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1427.7 lumens
Efficiency: N/A
Efficacy: 99.8 lumens/watt
Spacing Criteria (0/90/45): 0.39 / 0.39 / 0.35
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 14.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P223109

CATALOG NUMBER: LD2B15D010 EU2B15NFL258050 2LBD*GPH

Luminous Intensity Polar Plot





TEST NUMBER: P223109

CATALOG NUMBER: LD2B15D010 EU2B15NFL258050 2LBD*GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10			50	30	10			0
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111			106	106	106			100
1	115	113	112	110		113	111	110	108		107	106	105			104	103	102			97
2	112	109	106	104		110	107	104	102		104	102	100			101	99	98			95
3	109	105	101	99		107	103	100	98		101	98	96			99	97	95			92
4	106	101	97	95		104	100	97	94		98	95	93			96	94	92			90
5	103	98	94	91		102	97	94	91		95	92	90			94	91	89			88
6	101	95	91	89		99	94	91	88		93	90	88			92	89	87			86
7	98	92	89	86		97	92	88	86		91	88	85			90	87	85			84
8	96	90	86	84		95	90	86	84		89	86	83			88	85	83			82
9	94	88	84	82		93	88	84	82		87	84	82			86	83	81			80
10	92	86	82	80		91	86	82	80		85	82	80			84	82	80			79

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	3280821
5°	3029262
10°	2050424
15°	697597
20°	256227
25°	135824
30°	69819
35°	32580
40°	10669
45°	5368
50°	2531
55°	945
60°	1085
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P223109

CATALOG NUMBER: LD2B15D010 EU2B15NFL258050 2LBD*GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	662.7	46.4
10°-20°	557.2	39.0
20°-30°	152.9	10.7
30°-40°	44.6	3.1
40°-50°	8.2	0.6
50°-60°	1.9	0.1
60°-70°	0.2	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1372.8	96.2
0°-40°	1417.4	99.3
0°-60°	1427.5	100.0
0°-90°	1427.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1427.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	8470	
5°	7791	663
15°	1740	557
25°	318	153
35°	69	45
45°	10	8
55°	1	2
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P223109

CATALOG NUMBER: LD2B15D010 EU2B15NFL258050 2LBD*GPH

CANDELA DISTRIBUTION (FULL):

	0°
0°	8470.0
1°	8420.8
2°	8333.6
3°	8208.4
4°	8036.9
5°	7790.8
6°	7454.7
7°	7034.2
8°	6520.9
9°	5914.8
10°	5213.1
11°	4443.8
12°	3643.7
13°	2880.1
14°	2228.9
15°	1739.6
17.5°	981.6
20°	621.6
22.5°	443.0
25°	317.8
27.5°	225.0
30°	156.1
32.5°	109.7
35°	68.9
37.5°	28.1
40°	21.1
42.5°	15.5
45°	9.8
47.5°	5.6
50°	4.2
52.5°	2.8
55°	1.4
57.5°	1.4
60°	1.4
62.5°	0.0
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0



TEST NUMBER: P223109

CATALOG NUMBER: LD2B15D010 EU2B15NFL258050 2LBD*GPH

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







85°	0.0
87.5°	0.0



(END OF REPORT)