

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P#

Luminaire Tested: **LD2B15D010 EU2B15WFL558050 2LBDL*WH**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P#
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P14804)
Test Lab: INNOVATION CENTER(G1)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD2B15D010 EU2B15WFL558050 2LBDL*WH
Description: 1500 Lumen, 2inch Portfolio LED Downlight
WIDE FLOOD OPTIC
LENSED SPUN ROUND TRIM WITH WHEAT HAZE FINISH
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1249.9 lumens
Efficiency: N/A
Efficacy: 87.4 lumens/watt
Spacing Criteria (0/90/45): 0.75 / 0.75 / 0.81
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 14.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P#

CATALOG NUMBER: LD2B15D010 EU2B15WFL558050 2LBDL*WH

Luminous Intensity Polar Plot





TEST NUMBER: P#

CATALOG NUMBER: LD2B15D010 EU2B15WFL558050 2LBDL*WH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	111	108	106	111	108	106	104	104	103	101		101	99	98		97
2	108	103	99	95	105	101	97	94	98	95	92		95	92	90		92
3	102	96	90	86	100	94	90	86	92	88	84		89	86	83		87
4	97	89	83	79	95	88	83	79	86	81	78		84	80	77		82
5	92	83	77	73	90	82	77	73	80	76	72		79	75	71		77
6	87	78	72	68	86	77	71	67	76	71	67		74	70	66		73
7	83	73	67	63	81	73	67	63	71	66	62		70	65	62		69
8	79	69	63	59	77	68	63	59	67	62	58		66	61	58		65
9	75	65	59	55	74	64	59	55	64	58	55		63	58	54		62
10	71	61	56	52	70	61	55	52	60	55	51		59	55	51		59

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	625680
5°	604041
10°	546874
15°	479087
20°	412535
25°	350673
30°	275652
35°	191556
40°	124136
45°	74280
50°	43448
55°	24311
60°	9296
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P#

CATALOG NUMBER: LD2B15D010 EU2B15WFL558050 2LBDL*WH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	143.0	11.4
10°-20°	332.6	26.6
20°-30°	372.7	29.8
30°-40°	256.1	20.5
40°-50°	110.0	8.8
50°-60°	33.6	2.7
60°-70°	1.9	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	848.3	67.9
0°-40°	1104.4	88.4
0°-60°	1248.0	99.9
0°-90°	1249.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1249.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1615	
5°	1554	143
15°	1195	333
25°	820	373
35°	405	256
45°	136	110
55°	36	34
65°	0	2
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P#

CATALOG NUMBER: LD2B15D010 EU2B15WFL558050 2LBDL*WH

CANDELA DISTRIBUTION (FULL):

	0°
0°	1615.3
2.5°	1598.1
5°	1553.5
7.5°	1481.4
10°	1390.4
12.5°	1294.3
15°	1194.7
17.5°	1090.0
20°	1000.8
22.5°	911.5
25°	820.5
27.5°	724.4
30°	616.3
32.5°	506.4
35°	405.1
37.5°	317.6
40°	245.5
42.5°	183.7
45°	135.6
47.5°	99.6
50°	72.1
52.5°	49.8
55°	36.0
57.5°	24.0
60°	12.0
62.5°	1.7
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)