

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P264458

Luminaire Tested: **LD2B15D010 EU2B1510SP159050 2LBD*LI**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P264458
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1805-787-1)
Test Lab: INNOVATION CENTER(G2)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD2B15D010 EU2B1510SP159050 2LBD*LI
Description: 1500 Lumen, 2inch Portfolio LED Downlight
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1139.0 lumens
Efficiency: N/A
Efficacy: 79.7 lumens/watt
Spacing Criteria (0/90/45): 0.28 / 0.28 / 0.28
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 14.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P264458

CATALOG NUMBER: LD2B15D010 EU2B1510SP159050 2LBD*LI

Luminous Intensity Polar Plot





TEST NUMBER: P264458

CATALOG NUMBER: LD2B15D010 EU2B1510SP159050 2LBD*LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	116	114	112	111	113	112	110	109	108	107	106		104	103	102		101
2	113	109	107	105	111	108	106	104	105	103	101		102	101	99		99
3	110	106	103	100	108	105	102	100	102	100	98		100	98	97		98
4	107	103	99	97	106	102	99	96	100	97	95		98	96	94		96
5	105	100	97	94	104	99	96	94	98	95	93		96	94	92		95
6	103	98	94	92	102	97	94	91	96	93	91		95	92	90		93
7	101	95	92	90	100	95	92	89	94	91	89		93	90	89		92
8	99	93	90	88	98	93	90	88	92	89	87		91	89	87		91
9	97	92	88	86	96	91	88	86	91	88	86		90	87	86		89
10	95	90	87	85	95	90	87	85	89	86	85		89	86	84		88

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	5374486
5°	4307900
10°	1880251
15°	582682
20°	203132
25°	89711
30°	40619
35°	21140
40°	12044
45°	5721
50°	3607
55°	1978
60°	1184
65°	1401
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P264458

CATALOG NUMBER: LD2B15D010 EU2B1510SP159050 2LBD*LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	660.6	58.0
10°-20°	361.8	31.8
20°-30°	82.5	7.2
30°-40°	23.7	2.1
40°-50°	7.3	0.6
50°-60°	2.2	0.2
60°-70°	1.0	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1104.8	97.0
0°-40°	1128.5	99.1
0°-60°	1138.0	99.9
0°-90°	1139.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1139.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	10894	
5°	8698	661
15°	1141	362
25°	165	82
35°	35	24
45°	8	7
55°	2	2
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P264458

CATALOG NUMBER: LD2B15D010 EU2B1510SP159050 2LBD*LI

CANDELA DISTRIBUTION (FULL):

	0°
0°	10893.6
1°	10758.0
2°	10476.3
3°	10039.2
4°	9438.4
5°	8698.5
6°	7791.5
7°	6778.1
8°	5720.3
9°	4696.4
10°	3753.2
11°	2954.8
12°	2326.0
13°	1830.4
14°	1445.9
15°	1140.8
16°	900.0
17°	716.5
18°	576.2
19°	468.7
20°	386.9
22.5°	250.1
25°	164.8
26°	139.1
27°	118.1
28°	99.4
29°	83.0
30°	71.3
32.5°	49.1
35°	35.1
37.5°	25.7
40°	18.7
42.5°	12.9
45°	8.2
47.5°	5.8
50°	4.7
52.5°	3.5
55°	2.3
57.5°	1.2
60°	1.2
62.5°	1.2
65°	1.2
67.5°	1.2



TEST NUMBER: P264458

CATALOG NUMBER: LD2B15D010 EU2B1510SP159050 2LBD*LI

CANDELA DISTRIBUTION (continued):

	0°
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







70°	0.0
72.5°	0.0



(END OF REPORT)