

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P225329

Luminaire Tested: **LD2B15D010 EU2B15FL409050 2LBDC*MW**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P225329
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P14835)
Test Lab: INNOVATION CENTER (G1)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD2B15D010 EU2B15FL409050 2LBDC*MW
Description: 1500 Lumen, 2inch Portfolio LED Downlight
FLOOD OPTIC
CAST ROUND TRIM WITH MATTE WHITE FINISH
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1056.1 lumens
Efficiency: N/A
Efficacy: 73.9 lumens/watt
Spacing Criteria (0/90/45): 0.61 / 0.61 / 0.59
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 14.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P225329

CATALOG NUMBER: LD2B15D010 EU2B15FL409050 2LBDC*MW

Luminous Intensity Polar Plot





TEST NUMBER: P225329

CATALOG NUMBER: LD2B15D010 EU2B15FL409050 2LBDC*MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					0
RW	70	50	30	10		70	50	30	10		50	30	10			50	30	10			0
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111			106	106	106			100
1	114	112	110	108		112	110	108	106		106	104	103			102	101	100			95
2	110	106	102	99		108	104	101	98		101	98	96			98	96	94			91
3	105	100	96	93		104	99	95	92		96	93	90			94	91	89			86
4	101	95	90	87		100	94	90	86		92	88	85			90	87	85			82
5	98	91	86	82		96	90	85	82		88	84	81			86	83	80			79
6	94	86	82	78		93	86	81	78		84	80	77			83	79	77			75
7	90	83	78	74		89	82	77	74		81	77	74			80	76	73			72
8	87	79	74	71		86	79	74	71		78	74	71			77	73	70			69
9	84	76	71	68		83	76	71	68		75	71	68			74	70	67			66
10	81	73	68	65		80	73	68	65		72	68	65			71	68	65			64

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	956009
5°	938586
10°	834353
15°	656213
20°	436649
25°	250664
30°	126622
35°	59581
40°	23968
45°	11887
50°	6508
55°	4592
60°	4183
65°	2475
70°	3058
75°	2095
80°	3123
85°	0



TEST NUMBER: P225329

CATALOG NUMBER: LD2B15D010 EU2B15FL409050 2LBDC*MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	221.1	20.9
10°-20°	443.3	42.0
20°-30°	275.8	26.1
30°-40°	84.8	8.0
40°-50°	18.6	1.8
50°-60°	6.6	0.6
60°-70°	3.3	0.3
70°-80°	2.0	0.2
80°-90°	0.6	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	940.1	89.0
0°-40°	1024.9	97.0
0°-60°	1050.2	99.4
0°-90°	1056.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1056.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2468	
5°	2414	221
15°	1636	443
25°	586	276
35°	126	85
45°	22	19
55°	7	7
65°	3	3
75°	1	2
85°	0	1
90°	0	



TEST NUMBER: P225329

CATALOG NUMBER: LD2B15D010 EU2B15FL409050 2LBDC*MW

CANDELA DISTRIBUTION (FULL):

0°	
0°	2468.1
2.5°	2457.3
5°	2413.9
7.5°	2304.2
10°	2121.3
12.5°	1901.9
15°	1636.4
17.5°	1346.5
20°	1059.3
22.5°	803.3
25°	586.5
27.5°	413.2
30°	283.1
32.5°	191.0
35°	126.0
37.5°	75.9
40°	47.4
42.5°	32.5
45°	21.7
47.5°	14.9
50°	10.8
52.5°	9.5
55°	6.8
57.5°	5.4
60°	5.4
62.5°	4.1
65°	2.7
67.5°	2.7
70°	2.7
72.5°	2.7
75°	1.4
77.5°	1.4
80°	1.4
82.5°	1.4
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)