

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P224514

Luminaire Tested: **LD2B15D010 EU2B15FL409050 2LBDL*WMH**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P224514
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P14831)
Test Lab: INNOVATION CENTER (G1)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD2B15D010 EU2B15FL409050 2LBDL*WMH
Description: 1500 Lumen, 2inch Portfolio LED Downlight
FLOOD OPTIC
LENSED SPUN ROUND TRIM WITH WHEAT METALLIC HAZE FINISH
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1163.1 lumens
Efficiency: N/A
Efficacy: 81.3 lumens/watt
Spacing Criteria (0/90/45): 0.61 / 0.61 / 0.59
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 14.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P224514

CATALOG NUMBER: LD2B15D010 EU2B15FL409050 2LBDL*WMH

Luminous Intensity Polar Plot





TEST NUMBER: P224514

CATALOG NUMBER: LD2B15D010 EU2B15FL409050 2LBDL*WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					0
RW	70	50	30	10		70	50	30	10		50	30	10			50	30	10			0
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111			106	106	106			100
1	114	112	110	108		112	110	108	106		106	104	103			102	101	100			95
2	110	106	102	100		108	104	101	98		101	98	96			98	96	94			91
3	106	100	96	93		104	99	95	92		96	93	91			94	91	89			87
4	102	95	91	87		100	94	90	87		92	89	86			90	87	85			83
5	98	91	86	82		96	90	85	82		88	84	81			87	83	81			79
6	94	87	82	78		93	86	81	78		85	81	77			83	80	77			75
7	91	83	78	75		89	82	78	74		81	77	74			80	76	74			72
8	87	79	75	71		86	79	74	71		78	74	71			77	73	71			69
9	84	76	71	68		83	76	71	68		75	71	68			74	70	68			66
10	81	73	69	65		80	73	68	65		72	68	65			72	68	65			64

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1055402
5°	1033654
10°	915692
15°	719572
20°	483764
25°	281051
30°	140487
35°	66248
40°	31299
45°	13750
50°	7111
55°	3984
60°	2247
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P224514

CATALOG NUMBER: LD2B15D010 EU2B15FL409050 2LBDL*WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	243.2	20.9
10°-20°	486.7	41.8
20°-30°	307.7	26.5
30°-40°	96.3	8.3
40°-50°	22.3	1.9
50°-60°	5.9	0.5
60°-70°	1.1	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1037.6	89.2
0°-40°	1133.8	97.5
0°-60°	1162.0	99.9
0°-90°	1163.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1163.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2725	
5°	2658	243
15°	1794	487
25°	658	308
35°	140	96
45°	25	22
55°	6	6
65°	0	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P224514

CATALOG NUMBER: LD2B15D010 EU2B15FL409050 2LBDL*WMH

CANDELA DISTRIBUTION (FULL):

	0°
0°	2724.7
2.5°	2711.5
5°	2658.4
7.5°	2533.1
10°	2328.1
12.5°	2084.8
15°	1794.4
17.5°	1477.4
20°	1173.6
22.5°	893.5
25°	657.6
27.5°	464.4
30°	314.1
32.5°	209.4
35°	140.1
37.5°	94.4
40°	61.9
42.5°	38.3
45°	25.1
47.5°	17.7
50°	11.8
52.5°	8.8
55°	5.9
57.5°	4.4
60°	2.9
62.5°	2.9
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)