

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P#

Luminaire Tested: **LD2B15D010 EU2B15WFL559050 2LBDSQLC*MW**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P#
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P14810)
Test Lab: INNOVATION CENTER (G1)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD2B15D010 EU2B15WFL559050 2LBDSQLC*MW
Description: 1500 Lumen, 2inch Portfolio LED Downlight
WIDE FLOOD OPTIC
LENSED SQUARE CAST TRIM WITH MATTE WHITE FINISH
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1013.0 lumens
Efficiency: N/A
Efficacy: 70.8 lumens/watt
Spacing Criteria (0/90/45): 0.79 / 0.79 / 0.84
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 14.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P#

CATALOG NUMBER: LD2B15D010 EU2B15WFL559050 2LBDSQLC*MW

Luminous Intensity Polar Plot





TEST NUMBER: P#

CATALOG NUMBER: LD2B15D010 EU2B15WFL559050 2LBDSQLC*MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10			50	30	10			0
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111			106	106	106			100
1	113	110	108	106		111	108	106	104		104	102	101			101	99	98			93
2	108	102	98	95		105	101	97	94		98	94	92			95	92	90			86
3	102	95	90	86		100	94	89	85		91	87	84			89	85	83			80
4	97	89	83	79		95	88	82	78		85	81	77			83	80	76			74
5	91	83	77	72		90	82	76	72		80	75	71			78	74	71			69
6	87	78	71	67		85	77	71	67		75	70	66			74	69	66			64
7	82	73	67	62		81	72	66	62		71	66	62			70	65	62			60
8	78	69	62	58		77	68	62	58		67	62	58			66	61	58			56
9	74	65	59	55		73	64	58	54		63	58	54			62	57	54			53
10	71	61	55	51		70	61	55	51		60	55	51			59	54	51			49

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	475157
5°	472112
10°	438907
15°	385290
20°	332155
25°	284043
30°	225423
35°	157132
40°	99410
45°	60695
50°	35855
55°	19652
60°	4261
65°	3849
70°	3171
75°	4190
80°	3123
85°	6222



TEST NUMBER: P#

CATALOG NUMBER: LD2B15D010 EU2B15WFL559050 2LBDSQLC*MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	112.7	11.1
10°-20°	267.6	26.4
20°-30°	301.9	29.8
30°-40°	208.9	20.6
40°-50°	89.0	8.8
50°-60°	25.8	2.5
60°-70°	3.8	0.4
70°-80°	2.4	0.2
80°-90°	1.0	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	682.2	67.3
0°-40°	891.1	88.0
0°-60°	1005.8	99.3
0°-90°	1013.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1013.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1227	
5°	1214	113
15°	961	268
25°	665	302
35°	332	209
45°	111	89
55°	29	26
65°	4	4
75°	3	2
85°	1	1
90°	0	



TEST NUMBER: P#

CATALOG NUMBER: LD2B15D010 EU2B15WFL559050 2LBDSQLC*MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	1226.7
2.5°	1225.3
5°	1214.2
7.5°	1176.8
10°	1115.9
12.5°	1041.1
15°	960.8
17.5°	877.8
20°	805.8
22.5°	737.9
25°	664.6
27.5°	587.0
30°	504.0
32.5°	414.0
35°	332.3
37.5°	257.5
40°	196.6
42.5°	148.1
45°	110.8
47.5°	80.3
50°	59.5
52.5°	42.9
55°	29.1
57.5°	12.5
60°	5.5
62.5°	4.2
65°	4.2
67.5°	2.8
70°	2.8
72.5°	2.8
75°	2.8
77.5°	1.4
80°	1.4
82.5°	1.4
85°	1.4
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)