

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P264220

Luminaire Tested: **LD2B20D010 EU2B2010SP159024 2LBDC*MMS**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P264220
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1805-787-1)
Test Lab: INNOVATION CENTER(G2)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD2B20D010 EU2B2010SP159024 2LBDC*MMS
Description: 2000 Lumen, 2inch Portfolio LED Downlight
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1199.0 lumens
Efficiency: N/A
Efficacy: 57.4 lumens/watt
Spacing Criteria (0/90/45): 0.28 / 0.28 / 0.28
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 20.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P264220

CATALOG NUMBER: LD2B20D010 EU2B2010SP159024 2LBDC*MMS

Luminous Intensity Polar Plot





TEST NUMBER: P264220

CATALOG NUMBER: LD2B20D010 EU2B2010SP159024 2LBDC*MMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10			50	30	10			0
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111			106	106	106			100
1	116	114	112	111		113	112	110	109		108	107	106			104	103	102			98
2	113	109	107	105		111	108	106	104		105	103	101			102	101	99			96
3	110	106	103	100		108	105	102	100		102	100	98			100	98	97			94
4	107	103	99	97		106	102	99	96		100	97	95			98	96	94			92
5	105	100	97	94		104	99	96	94		98	95	93			96	94	92			90
6	103	98	94	92		102	97	94	91		96	93	91			95	92	90			89
7	101	95	92	90		100	95	92	89		94	91	89			93	90	89			87
8	99	93	90	88		98	93	90	88		92	89	87			91	89	87			86
9	97	92	88	86		96	91	88	86		91	88	86			90	87	86			85
10	95	90	87	85		95	90	87	85		89	86	85			89	86	84			83

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	5657626
5°	4534872
10°	1979293
15°	613379
20°	213843
25°	94447
30°	42783
35°	22224
40°	12688
45°	6000
50°	3761
55°	2150
60°	1184
65°	1401
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P264220

CATALOG NUMBER: LD2B20D010 EU2B2010SP159024 2LBDC*MMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	695.4	58.0
10°-20°	380.8	31.8
20°-30°	86.8	7.2
30°-40°	25.0	2.1
40°-50°	7.7	0.6
50°-60°	2.3	0.2
60°-70°	1.0	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1163.0	97.0
0°-40°	1187.9	99.1
0°-60°	1197.9	99.9
0°-90°	1199.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1199.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	11468	
5°	9157	695
15°	1201	381
25°	174	87
35°	37	25
45°	9	8
55°	2	2
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P264220

CATALOG NUMBER: LD2B20D010 EU2B2010SP159024 2LBDC*MMS

CANDELA DISTRIBUTION (FULL):

	0°
0°	11467.5
1°	11324.7
2°	11028.2
3°	10568.0
4°	9935.6
5°	9156.8
6°	8202.0
7°	7135.2
8°	6021.7
9°	4943.8
10°	3950.9
11°	3110.5
12°	2448.5
13°	1926.8
14°	1522.0
15°	1200.9
16°	947.4
17°	754.2
18°	606.6
19°	493.4
20°	407.3
22.5°	263.3
25°	173.5
26°	146.4
27°	124.3
28°	104.6
29°	87.4
30°	75.1
32.5°	51.7
35°	36.9
37.5°	27.1
40°	19.7
42.5°	13.5
45°	8.6
47.5°	6.2
50°	4.9
52.5°	3.7
55°	2.5
57.5°	1.2
60°	1.2
62.5°	1.2
65°	1.2
67.5°	1.2



TEST NUMBER: P264220

CATALOG NUMBER: LD2B20D010 EU2B2010SP159024 2LBDC*MMS

CANDELA DISTRIBUTION (continued):

	0°
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







70°	0.0
72.5°	0.0



(END OF REPORT)