

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P224680

Luminaire Tested: **LD2B20D010 EU2B20FL409024 2LBDLC*MW**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P224680
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P14835)
Test Lab: INNOVATION CENTER (G1)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD2B20D010 EU2B20FL409024 2LBDLC*MW
Description: 2000 Lumen, 2inch Portfolio LED Downlight
FLOOD OPTIC
LENSED CAST ROUND TRIM WITH MATTE WHITE FINISH
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1235.6 lumens
Efficiency: N/A
Efficacy: 59.1 lumens/watt
Spacing Criteria (0/90/45): 0.61 / 0.61 / 0.59
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 20.9
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P224680

CATALOG NUMBER: LD2B20D010 EU2B20FL409024 2LBDLC*MW

Luminous Intensity Polar Plot





TEST NUMBER: P224680

CATALOG NUMBER: LD2B20D010 EU2B20FL409024 2LBDLC*MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	114	112	110	108	112	110	108	106	106	104	103		102	101	100		99
2	110	106	102	99	108	104	101	98	101	98	96		98	96	94		95
3	105	100	96	93	104	99	95	92	96	93	90		94	91	89		92
4	101	95	90	87	100	94	90	86	92	88	85		90	87	85		88
5	98	91	86	82	96	90	85	82	88	84	81		86	83	80		85
6	94	86	82	78	93	86	81	78	84	80	77		83	79	77		82
7	90	83	78	74	89	82	77	74	81	77	74		80	76	73		79
8	87	79	74	71	86	79	74	71	78	74	71		77	73	70		76
9	84	76	71	68	83	76	71	68	75	71	68		74	70	67		73
10	81	73	68	65	80	73	68	65	72	68	65		71	68	65		71

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1118500
5°	1098121
10°	976184
15°	767734
20°	510887
25°	293274
30°	148135
35°	69700
40°	28063
45°	13914
50°	7653
55°	5335
60°	4881
65°	2933
70°	3624
75°	2395
80°	3569
85°	0



TEST NUMBER: P224680

CATALOG NUMBER: LD2B20D010 EU2B20FL409024 2LBDLC*MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	258.7	20.9
10°-20°	518.6	42.0
20°-30°	322.6	26.1
30°-40°	99.2	8.0
40°-50°	21.8	1.8
50°-60°	7.7	0.6
60°-70°	3.9	0.3
70°-80°	2.3	0.2
80°-90°	0.7	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1099.9	89.0
0°-40°	1199.1	97.1
0°-60°	1228.6	99.4
0°-90°	1235.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1235.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2888	
5°	2824	259
15°	1914	519
25°	686	323
35°	147	99
45°	25	22
55°	8	8
65°	3	4
75°	2	2
85°	0	1
90°	0	



TEST NUMBER: P224680

CATALOG NUMBER: LD2B20D010 EU2B20FL409024 2LBDLC*MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	2887.6
2.5°	2875.0
5°	2824.2
7.5°	2695.9
10°	2481.9
12.5°	2225.2
15°	1914.5
17.5°	1575.4
20°	1239.4
22.5°	939.8
25°	686.2
27.5°	483.4
30°	331.2
32.5°	223.5
35°	147.4
37.5°	88.8
40°	55.5
42.5°	38.0
45°	25.4
47.5°	17.4
50°	12.7
52.5°	11.1
55°	7.9
57.5°	6.3
60°	6.3
62.5°	4.8
65°	3.2
67.5°	3.2
70°	3.2
72.5°	3.2
75°	1.6
77.5°	1.6
80°	1.6
82.5°	1.6
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)