

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P224433

Luminaire Tested: **LD2B20D010 EU2B20FL408027 2LBDSQC*MW**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P224433
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P14831)
Test Lab: INNOVATION CENTER (G1)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD2B20D010 EU2B20FL408027 2LBDSQC*MW
Description: 2000 Lumen, 2inch Portfolio LED Downlight
FLOOD OPTIC
SQUARE CAST TRIM WITH MATTE WHITE FINISH
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1822.6 lumens
Efficiency: N/A
Efficacy: 87.2 lumens/watt
Spacing Criteria (0/90/45): 0.61 / 0.61 / 0.59
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 20.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P224433

CATALOG NUMBER: LD2B20D010 EU2B20FL408027 2LBDSQC*MW

Luminous Intensity Polar Plot





TEST NUMBER: P224433

CATALOG NUMBER: LD2B20D010 EU2B20FL408027 2LBDSQC*MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	114	112	110	108	112	110	108	106	106	104	103		102	101	100		99
2	110	106	102	99	108	104	101	98	101	98	96		98	96	94		95
3	105	100	96	93	104	99	95	92	96	93	90		94	91	89		92
4	101	95	90	87	100	94	90	86	92	88	85		90	87	85		88
5	98	91	86	82	96	90	85	82	88	84	81		86	83	80		85
6	94	86	82	78	93	86	81	78	84	80	77		83	79	77		82
7	90	83	78	74	89	82	77	74	81	77	74		80	76	73		79
8	87	79	74	71	86	79	74	71	78	74	71		77	73	70		76
9	84	76	71	68	83	76	71	68	75	71	68		74	70	67		73
10	81	73	68	65	80	73	68	65	72	68	65		71	68	65		71

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1650055
5°	1620003
10°	1440107
15°	1132613
20°	753634
25°	432689
30°	218580
35°	102800
40°	41362
45°	20487
50°	11269
55°	7901
60°	7282
65°	4308
70°	5323
75°	3442
80°	5130
85°	0



TEST NUMBER: P224433

CATALOG NUMBER: LD2B20D010 EU2B20FL408027 2LBDSQC*MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	381.6	20.9
10°-20°	765.1	42.0
20°-30°	476.0	26.1
30°-40°	146.3	8.0
40°-50°	32.1	1.8
50°-60°	11.5	0.6
60°-70°	5.8	0.3
70°-80°	3.4	0.2
80°-90°	0.9	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1622.6	89.0
0°-40°	1768.9	97.1
0°-60°	1812.6	99.4
0°-90°	1822.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1822.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4260	
5°	4166	382
15°	2824	765
25°	1012	476
35°	217	146
45°	37	32
55°	12	11
65°	5	6
75°	2	3
85°	0	1
90°	0	



TEST NUMBER: P224433

CATALOG NUMBER: LD2B20D010 EU2B20FL408027 2LBDSQC*MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	4259.9
2.5°	4241.2
5°	4166.4
7.5°	3977.0
10°	3661.4
12.5°	3282.6
15°	2824.4
17.5°	2324.0
20°	1828.3
22.5°	1386.5
25°	1012.4
27.5°	713.1
30°	488.7
32.5°	329.7
35°	217.4
37.5°	130.9
40°	81.8
42.5°	56.1
45°	37.4
47.5°	25.7
50°	18.7
52.5°	16.4
55°	11.7
57.5°	9.4
60°	9.4
62.5°	7.0
65°	4.7
67.5°	4.7
70°	4.7
72.5°	4.7
75°	2.3
77.5°	2.3
80°	2.3
82.5°	2.3
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)