

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P264737

Luminaire Tested: **LD2B20D010 EU2B2010SP158035 2LBDL*B**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P264737
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1711-432-2)
Test Lab: INNOVATION CENTER(G3)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD2B20D010 EU2B2010SP158035 2LBDL*B
Description: 2000 Lumen, 2inch Portfolio LED Downlight
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1721.0 lumens
Efficiency: N/A
Efficacy: 82.3 lumens/watt
Spacing Criteria (0/90/45): 0.31 / 0.31 / 0.32
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 20.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P264737

CATALOG NUMBER: LD2B20D010 EU2B2010SP158035 2LBDL*B

Luminous Intensity Polar Plot





TEST NUMBER: P264737

CATALOG NUMBER: LD2B20D010 EU2B2010SP158035 2LBDL*B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	115	113	111	110	113	111	110	108	107	106	105		104	103	102		100
2	112	108	106	103	110	107	104	102	104	102	100		101	99	98		98
3	109	104	101	98	107	103	100	97	100	98	96		98	96	94		96
4	105	100	97	94	104	99	96	93	97	95	92		96	93	91		94
5	103	97	93	91	101	96	93	90	95	92	89		93	91	89		92
6	100	94	90	88	99	94	90	87	92	89	87		91	88	86		90
7	98	92	88	85	97	91	88	85	90	87	85		89	86	84		88
8	95	89	86	83	94	89	85	83	88	85	82		87	84	82		86
9	93	87	83	81	92	87	83	81	86	83	81		85	82	80		85
10	91	85	82	79	91	85	81	79	84	81	79		84	81	79		83

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	6075504
5°	4944837
10°	2671086
15°	1065049
20°	427055
25°	204518
30°	106018
35°	56073
40°	31107
45°	19257
50°	13202
55°	8860
60°	6808
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P264737

CATALOG NUMBER: LD2B20D010 EU2B2010SP158035 2LBDL*B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	803.0	46.7
10°-20°	633.5	36.8
20°-30°	186.9	10.9
30°-40°	62.2	3.6
40°-50°	23.4	1.4
50°-60°	10.3	0.6
60°-70°	1.7	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1623.4	94.3
0°-40°	1685.6	97.9
0°-60°	1719.4	99.9
0°-90°	1721.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1721.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	12314	
5°	9985	803
15°	2085	634
25°	376	187
35°	93	62
45°	28	23
55°	10	10
65°	0	2
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P264737

CATALOG NUMBER: LD2B20D010 EU2B2010SP158035 2LBDL*B

CANDELA DISTRIBUTION (FULL):

0°	
0°	12314.5
2.5°	11818.2
5°	9984.6
7.5°	7692.7
10°	5331.8
12.5°	3412.1
15°	2085.2
17.5°	1271.8
20°	813.4
22.5°	544.6
25°	375.7
27.5°	265.4
30°	186.1
32.5°	131.0
35°	93.1
37.5°	65.5
40°	48.3
42.5°	37.9
45°	27.6
47.5°	24.1
50°	17.2
52.5°	13.8
55°	10.3
57.5°	10.3
60°	6.9
62.5°	3.4
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)