

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P264732

Luminaire Tested: **LD2B20D010 EU2B2010SP158035 2LBDL*H**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P264732
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1711-432-2)
Test Lab: INNOVATION CENTER(G3)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD2B20D010 EU2B2010SP158035 2LBDL*H
Description: 2000 Lumen, 2inch Portfolio LED Downlight
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1689.0 lumens
Efficiency: N/A
Efficacy: 80.8 lumens/watt
Spacing Criteria (0/90/45): 0.31 / 0.31 / 0.32
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 20.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P264732

CATALOG NUMBER: LD2B20D010 EU2B2010SP158035 2LBDL*H

Luminous Intensity Polar Plot





TEST NUMBER: P264732

CATALOG NUMBER: LD2B20D010 EU2B2010SP158035 2LBDL*H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0			
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	115	113	111	110	113	111	110	108	107	106	105	104	103	102	100	99	99	97			
2	112	108	106	103	110	107	104	102	104	102	100	101	99	98	98	97	96	94			
3	109	104	101	98	107	103	100	97	100	98	96	98	96	94	96	94	93	92			
4	105	100	97	94	104	99	96	93	97	95	92	96	93	91	94	92	90	89			
5	103	97	93	91	101	96	93	90	95	92	89	93	91	89	92	90	88	87			
6	100	94	90	88	99	94	90	87	92	89	87	91	88	86	90	88	86	85			
7	98	92	88	85	97	91	88	85	90	87	85	89	86	84	88	86	84	83			
8	95	89	86	83	94	89	85	83	88	85	82	87	84	82	86	84	82	81			
9	93	87	83	81	92	87	83	81	86	83	81	85	82	80	85	82	80	79			
10	91	85	82	79	91	85	81	79	84	81	79	84	81	79	83	80	78	78			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	5962524
5°	4852869
10°	2621390
15°	1045231
20°	419127
25°	200707
30°	104081
35°	54988
40°	30527
45°	18908
50°	12971
55°	8688
60°	6710
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P264732

CATALOG NUMBER: LD2B20D010 EU2B2010SP158035 2LBDL*H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	788.0	46.7
10°-20°	621.8	36.8
20°-30°	183.4	10.9
30°-40°	61.1	3.6
40°-50°	23.0	1.4
50°-60°	10.1	0.6
60°-70°	1.6	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1593.2	94.3
0°-40°	1654.3	97.9
0°-60°	1687.4	99.9
0°-90°	1689.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1689.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	12086	
5°	9799	788
15°	2046	622
25°	369	183
35°	91	61
45°	27	23
55°	10	10
65°	0	2
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P264732

CATALOG NUMBER: LD2B20D010 EU2B2010SP158035 2LBDL*H

CANDELA DISTRIBUTION (FULL):

	0°
0°	12085.5
2.5°	11598.4
5°	9798.9
7.5°	7549.6
10°	5232.6
12.5°	3348.6
15°	2046.4
17.5°	1248.1
20°	798.3
22.5°	534.4
25°	368.7
27.5°	260.4
30°	182.7
32.5°	128.5
35°	91.3
37.5°	64.3
40°	47.4
42.5°	37.2
45°	27.1
47.5°	23.7
50°	16.9
52.5°	13.5
55°	10.1
57.5°	10.1
60°	6.8
62.5°	3.4
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)