

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P224280

Luminaire Tested: **LD2B20D010 EU2B20FL408035 2LBDSQLC*MMS**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P224280
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P14836)
Test Lab: INNOVATION CENTER (G1)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD2B20D010 EU2B20FL408035 2LBDSQLC*MMS
Description: 2000 Lumen, 2inch Portfolio LED Downlight
FLOOD OPTIC
LENSED SQUARE CAST TRIM WITH MATTE METALLIC SILVER
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1659.5 lumens
Efficiency: N/A
Efficacy: 79.4 lumens/watt
Spacing Criteria (0/90/45): 0.61 / 0.61 / 0.59
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 20.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P224280

CATALOG NUMBER: LD2B20D010 EU2B20FL408035 2LBDSQLC*MMS

Luminous Intensity Polar Plot





TEST NUMBER: P224280

CATALOG NUMBER: LD2B20D010 EU2B20FL408035 2LBDSQLC*MMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10			50	30	10			0
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111			106	106	106			100
1	114	112	110	108		112	110	108	106		106	104	103			102	101	100			95
2	110	106	102	100		108	104	101	99		101	99	96			98	96	94			91
3	106	100	96	93		104	99	95	92		97	93	91			94	92	89			87
4	102	95	91	87		100	94	90	87		92	89	86			90	87	85			83
5	98	91	86	83		96	90	86	82		88	85	82			87	83	81			79
6	94	87	82	78		93	86	82	78		85	81	78			83	80	77			76
7	91	83	78	75		89	82	78	75		81	77	74			80	77	74			72
8	87	80	75	71		86	79	75	71		78	74	71			77	73	71			69
9	84	76	72	68		83	76	71	68		75	71	68			74	71	68			67
10	81	74	69	66		81	73	69	66		72	68	65			72	68	65			64

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1510572
5°	1481581
10°	1316093
15°	1038576
20°	692710
25°	398711
30°	201942
35°	94667
40°	38783
45°	17474
50°	8979
55°	5740
60°	3331
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P224280

CATALOG NUMBER: LD2B20D010 EU2B20FL408035 2LBDSQLC*MMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	348.8	21.0
10°-20°	699.9	42.2
20°-30°	438.4	26.4
30°-40°	135.7	8.2
40°-50°	28.0	1.7
50°-60°	7.8	0.5
60°-70°	1.0	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1487.0	89.6
0°-40°	1622.6	97.8
0°-60°	1658.4	99.9
0°-90°	1659.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1659.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3900	
5°	3810	349
15°	2590	700
25°	933	438
35°	200	136
45°	32	28
55°	8	8
65°	0	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P224280

CATALOG NUMBER: LD2B20D010 EU2B20FL408035 2LBDSQLC*MMS

CANDELA DISTRIBUTION (FULL):

	0°
0°	3899.8
2.5°	3880.7
5°	3810.4
7.5°	3631.5
10°	3346.1
12.5°	2994.6
15°	2589.9
17.5°	2123.5
20°	1680.5
22.5°	1277.9
25°	932.9
27.5°	656.0
30°	451.5
32.5°	302.4
35°	200.2
37.5°	125.7
40°	76.7
42.5°	49.0
45°	31.9
47.5°	21.3
50°	14.9
52.5°	10.6
55°	8.5
57.5°	6.4
60°	4.3
62.5°	2.1
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)