

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P224324

Luminaire Tested: **LD2B20D010 EU2B20FL408035 2LBDSQLC*MW**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P224324
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P14835)
Test Lab: INNOVATION CENTER (G1)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD2B20D010 EU2B20FL408035 2LBDSQLC*MW
Description: 2000 Lumen, 2inch Portfolio LED Downlight
FLOOD OPTIC
LENSED SQUARE CAST TRIM WITH MATTE WHITE FINISH
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1661.9 lumens
Efficiency: N/A
Efficacy: 79.5 lumens/watt
Spacing Criteria (0/90/45): 0.61 / 0.61 / 0.59
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 20.9
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P224324

CATALOG NUMBER: LD2B20D010 EU2B20FL408035 2LBDSQLC*MW

Luminous Intensity Polar Plot





TEST NUMBER: P224324

CATALOG NUMBER: LD2B20D010 EU2B20FL408035 2LBDSQLC*MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10			50	30	10			0
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111			106	106	106			100
1	114	112	110	108		112	110	108	106		106	104	103			102	101	100			95
2	110	106	102	99		108	104	101	98		101	98	96			98	96	94			91
3	105	100	96	93		104	99	95	92		96	93	90			94	91	89			86
4	101	95	90	87		100	94	90	86		92	88	85			90	87	85			82
5	98	91	86	82		96	90	85	82		88	84	81			86	83	80			79
6	94	86	82	78		93	86	81	78		84	80	77			83	79	77			75
7	90	83	78	74		89	82	77	74		81	77	74			80	76	73			72
8	87	79	74	71		86	79	74	71		78	74	71			77	73	70			69
9	84	76	71	68		83	76	71	68		75	71	68			74	70	67			66
10	81	73	68	65		80	73	68	65		72	68	65			71	68	65			64

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1504529
5°	1477110
10°	1313104
15°	1032721
20°	687187
25°	394523
30°	199303
35°	93769
40°	37721
45°	18680
50°	10305
55°	7226
60°	6585
65°	3941
70°	4870
75°	3143
80°	4684
85°	0



TEST NUMBER: P224324

CATALOG NUMBER: LD2B20D010 EU2B20FL408035 2LBDSQLC*MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	347.9	20.9
10°-20°	697.6	42.0
20°-30°	434.0	26.1
30°-40°	133.4	8.0
40°-50°	29.3	1.8
50°-60°	10.4	0.6
60°-70°	5.3	0.3
70°-80°	3.1	0.2
80°-90°	0.9	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1479.5	89.0
0°-40°	1613.0	97.1
0°-60°	1652.7	99.4
0°-90°	1661.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1661.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3884	
5°	3799	348
15°	2575	698
25°	923	434
35°	198	133
45°	34	29
55°	11	10
65°	4	5
75°	2	3
85°	0	1
90°	0	



TEST NUMBER: P224324

CATALOG NUMBER: LD2B20D010 EU2B20FL408035 2LBDSQLC*MW

CANDELA DISTRIBUTION (FULL):

0°	
0°	3884.2
2.5°	3867.2
5°	3798.9
7.5°	3626.3
10°	3338.5
12.5°	2993.1
15°	2575.3
17.5°	2119.1
20°	1667.1
22.5°	1264.2
25°	923.1
27.5°	650.2
30°	445.6
32.5°	300.6
35°	198.3
37.5°	119.4
40°	74.6
42.5°	51.2
45°	34.1
47.5°	23.5
50°	17.1
52.5°	14.9
55°	10.7
57.5°	8.5
60°	8.5
62.5°	6.4
65°	4.3
67.5°	4.3
70°	4.3
72.5°	4.3
75°	2.1
77.5°	2.1
80°	2.1
82.5°	2.1
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)