

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P223275

Luminaire Tested: **LD2B20D010 EU2B20NFL258035 2LBDSQLC*MW**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P223275
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (155)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD2B20D010 EU2B20NFL258035 2LBDSQLC*MW
Description: 2000 Lumen, 2inch Portfolio LED Downlight
NARROW FLOOD OPTIC
LENSED SQUARE CAST TRIM WITH MATTE WHITE FINISH
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1657.1 lumens
Efficiency: N/A
Efficacy: 79.3 lumens/watt
Spacing Criteria (0/90/45): 0.39 / 0.39 / 0.35
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 20.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P223275

CATALOG NUMBER: LD2B20D010 EU2B20NFL258035 2LBDSQLC*MW

Luminous Intensity Polar Plot





TEST NUMBER: P223275

CATALOG NUMBER: LD2B20D010 EU2B20NFL258035 2LBDSQLC*MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	115	113	112	110	113	111	110	108	107	106	105		104	103	102		100
2	112	109	106	104	110	107	104	102	104	102	100		101	99	98		98
3	109	105	101	99	107	103	100	98	101	98	96		99	97	95		96
4	106	101	97	95	104	100	97	94	98	95	93		96	94	92		95
5	103	98	94	91	102	97	94	91	95	92	90		94	91	89		93
6	101	95	91	89	99	94	91	88	93	90	88		92	89	87		91
7	98	92	89	86	97	92	88	86	91	88	85		90	87	85		89
8	96	90	86	84	95	90	86	84	89	86	83		88	85	83		87
9	94	88	84	82	93	88	84	82	87	84	82		86	83	81		85
10	92	86	82	80	91	86	82	80	85	82	80		84	82	80		84

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	3807960
5°	3515994
10°	2379870
15°	809679
20°	297365
25°	157664
30°	81045
35°	37829
40°	12388
45°	6245
50°	2953
55°	1081
60°	1240
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P223275

CATALOG NUMBER: LD2B20D010 EU2B20NFL258035 2LBDSQLC*MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	769.2	46.4
10°-20°	646.7	39.0
20°-30°	177.5	10.7
30°-40°	51.7	3.1
40°-50°	9.6	0.6
50°-60°	2.2	0.1
60°-70°	0.2	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1593.4	96.2
0°-40°	1645.2	99.3
0°-60°	1656.9	100.0
0°-90°	1657.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1657.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	9831	
5°	9043	769
15°	2019	647
25°	369	177
35°	80	52
45°	11	10
55°	2	2
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P223275

CATALOG NUMBER: LD2B20D010 EU2B20NFL258035 2LBDSQLC*MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	9830.9
1°	9773.8
2°	9672.6
3°	9527.4
4°	9328.2
5°	9042.6
6°	8652.5
7°	8164.4
8°	7568.7
9°	6865.2
10°	6050.7
11°	5157.9
12°	4229.1
13°	3342.8
14°	2587.1
15°	2019.1
17.5°	1139.3
20°	721.4
22.5°	514.2
25°	368.9
27.5°	261.2
30°	181.2
32.5°	127.3
35°	80.0
37.5°	32.6
40°	24.5
42.5°	18.0
45°	11.4
47.5°	6.5
50°	4.9
52.5°	3.3
55°	1.6
57.5°	1.6
60°	1.6
62.5°	0.0
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0



TEST NUMBER: P223275

CATALOG NUMBER: LD2B20D010 EU2B20NFL258035 2LBDSQLC*MW

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







85°	0.0
87.5°	0.0



(END OF REPORT)