

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P265053

Luminaire Tested: **LD2B20D010 EU2B2010SP159035 2LBSQLC*MB**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P265053
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1711-432-2)
Test Lab: INNOVATION CENTER(G3)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD2B20D010 EU2B2010SP159035 2LBSQLC*MB
Description: 2000 Lumen, 2inch Portfolio LED Downlight
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1400.0 lumens
Efficiency: N/A
Efficacy: 67.0 lumens/watt
Spacing Criteria (0/90/45): 0.31 / 0.31 / 0.32
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 20.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P265053

CATALOG NUMBER: LD2B20D010 EU2B2010SP159035 2LBSQLC*MB

Luminous Intensity Polar Plot





TEST NUMBER: P265053

CATALOG NUMBER: LD2B20D010 EU2B2010SP159035 2LBSQLC*MB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10			50	30	10			0
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111			106	106	106			100
1	115	113	111	110		113	111	110	108		107	106	105			104	103	102			97
2	112	108	106	103		110	107	104	102		104	102	100			101	99	98			94
3	109	104	101	98		107	103	100	97		100	98	96			98	96	94			92
4	106	100	97	94		104	99	96	93		97	95	92			96	93	91			89
5	103	97	93	91		101	96	93	90		95	92	89			93	91	89			87
6	100	94	90	88		99	94	90	87		92	89	87			91	88	86			85
7	98	92	88	85		97	91	88	85		90	87	85			89	86	84			83
8	95	89	86	83		94	89	85	83		88	85	82			87	84	82			81
9	93	87	83	81		92	87	83	81		86	83	81			85	82	80			79
10	91	85	82	79		91	85	81	79		84	81	79			84	81	79			78

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	4942301
5°	4022539
10°	2172869
15°	866361
20°	347409
25°	166358
30°	86250
35°	45593
40°	25311
45°	15629
50°	10745
55°	7225
60°	5526
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P265053

CATALOG NUMBER: LD2B20D010 EU2B2010SP159035 2LBSQLC*MB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	653.2	46.7
10°-20°	515.4	36.8
20°-30°	152.0	10.9
30°-40°	50.6	3.6
40°-50°	19.0	1.4
50°-60°	8.4	0.6
60°-70°	1.4	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1320.6	94.3
0°-40°	1371.2	97.9
0°-60°	1398.6	99.9
0°-90°	1400.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1400.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	10018	
5°	8122	653
15°	1696	515
25°	306	152
35°	76	51
45°	22	19
55°	8	8
65°	0	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P265053

CATALOG NUMBER: LD2B20D010 EU2B2010SP159035 2LBSQLC*MB

CANDELA DISTRIBUTION (FULL):

	0°
0°	10017.6
2.5°	9613.8
5°	8122.3
7.5°	6257.8
10°	4337.3
12.5°	2775.6
15°	1696.2
17.5°	1034.6
20°	661.7
22.5°	443.0
25°	305.6
27.5°	215.9
30°	151.4
32.5°	106.5
35°	75.7
37.5°	53.3
40°	39.3
42.5°	30.8
45°	22.4
47.5°	19.6
50°	14.0
52.5°	11.2
55°	8.4
57.5°	8.4
60°	5.6
62.5°	2.8
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)