

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P225159

Luminaire Tested: **LD2B20D010 EU2B20FL409035 2LBD*GPH**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P225159
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P14831)
Test Lab: INNOVATION CENTER (G1)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD2B20D010 EU2B20FL409035 2LBD*GPH
Description: 2000 Lumen, 2inch Portfolio LED Downlight
FLOOD OPTIC
SPUN ROUND TRIM WITH GRAPHITE FINISH
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1572.3 lumens
Efficiency: N/A
Efficacy: 75.2 lumens/watt
Spacing Criteria (0/90/45): 0.61 / 0.61 / 0.59
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 20.9
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P225159

CATALOG NUMBER: LD2B20D010 EU2B20FL409035 2LBD*GPH

Luminous Intensity Polar Plot





TEST NUMBER: P225159

CATALOG NUMBER: LD2B20D010 EU2B20FL409035 2LBD*GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	114	112	110	108		112	110	108	106		106	104	103		102	101	100		99	98	97
2	110	106	102	100		108	104	101	98		101	99	96		98	96	94		95	94	92
3	106	100	96	93		104	99	95	92		96	93	91		94	92	89		92	90	88
4	102	95	91	87		100	94	90	87		92	89	86		90	87	85		89	86	84
5	98	91	86	83		96	90	85	82		88	84	81		87	83	81		85	82	80
6	94	87	82	78		93	86	81	78		85	81	78		83	80	77		82	79	77
7	91	83	78	75		89	82	78	74		81	77	74		80	76	74		79	76	73
8	87	80	75	71		86	79	74	71		78	74	71		77	73	71		76	73	70
9	84	76	72	68		83	76	71	68		75	71	68		74	70	68		73	70	68
10	81	73	69	65		80	73	68	65		72	68	65		72	68	65		71	67	65

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1426324
5°	1397478
10°	1241755
15°	974254
20°	655241
25°	381231
30°	190984
35°	89087
40°	41564
45°	17584
50°	8436
55°	5403
60°	3099
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P225159

CATALOG NUMBER: LD2B20D010 EU2B20FL409035 2LBD*GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	329.0	20.9
10°-20°	659.5	41.9
20°-30°	417.0	26.5
30°-40°	129.7	8.3
40°-50°	28.8	1.8
50°-60°	7.3	0.5
60°-70°	1.0	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1405.4	89.4
0°-40°	1535.2	97.6
0°-60°	1571.3	99.9
0°-90°	1572.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1572.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3682	
5°	3594	329
15°	2430	659
25°	892	417
35°	188	130
45°	32	29
55°	8	7
65°	0	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P225159

CATALOG NUMBER: LD2B20D010 EU2B20FL409035 2LBD*GPH

CANDELA DISTRIBUTION (FULL):

0°	
0°	3682.3
2.5°	3666.3
5°	3594.1
7.5°	3423.7
10°	3157.1
12.5°	2820.4
15°	2429.5
17.5°	2006.5
20°	1589.6
22.5°	1214.7
25°	892.0
27.5°	625.4
30°	427.0
32.5°	282.6
35°	188.4
37.5°	126.3
40°	82.2
42.5°	50.1
45°	32.1
47.5°	22.0
50°	14.0
52.5°	10.0
55°	8.0
57.5°	6.0
60°	4.0
62.5°	2.0
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)