

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P225412

Luminaire Tested: **LD2B20D010 EU2B20FL409035 2LBDC*MB**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P225412
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P14834)
Test Lab: INNOVATION CENTER (G1)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD2B20D010 EU2B20FL409035 2LBDC*MB
Description: 2000 Lumen, 2inch Portfolio LED Downlight
FLOOD OPTIC
CAST ROUND TRIM WITH MATTE BLACK FINISH
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1545.6 lumens
Efficiency: N/A
Efficacy: 74.0 lumens/watt
Spacing Criteria (0/90/45): 0.61 / 0.61 / 0.6
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 20.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P225412

CATALOG NUMBER: LD2B20D010 EU2B20FL409035 2LBDC*MB

Luminous Intensity Polar Plot





TEST NUMBER: P225412

CATALOG NUMBER: LD2B20D010 EU2B20FL409035 2LBDC*MB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					0
RW	70	50	30	10		70	50	30	10		50	30	10			50	30	10			0
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111			106	106	106			100
1	114	112	110	108		112	110	108	106		106	104	103			102	101	100			95
2	110	106	103	100		108	104	101	99		101	99	96			98	96	94			91
3	106	100	96	93		104	99	95	92		97	93	91			94	92	89			87
4	102	95	91	87		100	94	90	87		92	89	86			90	87	85			83
5	98	91	86	83		96	90	86	82		88	85	82			87	84	81			79
6	94	87	82	79		93	86	82	78		85	81	78			84	80	77			76
7	91	83	78	75		90	83	78	75		81	77	74			80	77	74			72
8	87	80	75	72		86	79	75	71		78	74	71			77	74	71			69
9	84	77	72	69		83	76	72	68		75	71	68			74	71	68			67
10	82	74	69	66		81	73	69	66		73	68	65			72	68	65			64

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1398435
5°	1374149
10°	1225826
15°	968961
20°	646090
25°	374820
30°	187584
35°	88236
40°	34485
45°	15393
50°	7231
55°	4052
60°	1549
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P225412

CATALOG NUMBER: LD2B20D010 EU2B20FL409035 2LBDC*MB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	323.9	21.0
10°-20°	654.0	42.3
20°-30°	411.4	26.6
30°-40°	125.8	8.1
40°-50°	24.7	1.6
50°-60°	5.5	0.4
60°-70°	0.2	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1389.4	89.9
0°-40°	1515.1	98.0
0°-60°	1545.3	100.0
0°-90°	1545.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1545.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3610	
5°	3534	324
15°	2416	654
25°	877	411
35°	187	126
45°	28	25
55°	6	6
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P225412

CATALOG NUMBER: LD2B20D010 EU2B20FL409035 2LBDC*MB

CANDELA DISTRIBUTION (FULL):

	0°
0°	3610.3
2.5°	3602.3
5°	3534.1
7.5°	3373.5
10°	3116.6
12.5°	2795.6
15°	2416.3
17.5°	1994.8
20°	1567.4
22.5°	1202.1
25°	877.0
27.5°	618.1
30°	419.4
32.5°	283.0
35°	186.6
37.5°	114.4
40°	68.2
42.5°	44.2
45°	28.1
47.5°	18.1
50°	12.0
52.5°	8.0
55°	6.0
57.5°	4.0
60°	2.0
62.5°	0.0
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)