

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P#

Luminaire Tested: **LD2B20D010 EU2B20WFL559035 2LBDL*H**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P#
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P14807)
Test Lab: INNOVATION CENTER (G1)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD2B20D010 EU2B20WFL559035 2LBDL*H
Description: 2000 Lumen, 2inch Portfolio LED Downlight
WIDE FLOOD OPTIC
LENSED SPUN ROUND TRIM WITH HAZE FINISH
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1361.5 lumens
Efficiency: N/A
Efficacy: 65.1 lumens/watt
Spacing Criteria (0/90/45): 0.79 / 0.79 / 0.83
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 20.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P#

CATALOG NUMBER: LD2B20D010 EU2B20WFL559035 2LBDL*H

Luminous Intensity Polar Plot





TEST NUMBER: P#

CATALOG NUMBER: LD2B20D010 EU2B20WFL559035 2LBDL*H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	111	108	106	111	108	106	104	104	102	101		101	99	98		97
2	108	102	98	95	105	101	97	94	98	94	92		95	92	90		92
3	102	95	90	86	100	94	89	85	91	87	84		89	85	83		86
4	96	89	83	79	95	87	82	78	85	81	77		83	79	76		81
5	91	83	77	72	90	82	76	72	80	75	71		78	74	71		77
6	87	77	71	67	85	77	71	67	75	70	66		74	69	66		72
7	82	73	66	62	81	72	66	62	71	65	62		69	65	61		68
8	78	68	62	58	77	68	62	58	67	61	57		66	61	57		65
9	74	64	58	54	73	64	58	54	63	58	54		62	57	54		61
10	71	61	55	51	70	60	55	51	60	54	51		59	54	51		58

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	638695
5°	626320
10°	582194
15°	515458
20°	446253
25°	375119
30°	293766
35°	209904
40°	140165
45°	86934
50°	52065
55°	31200
60°	14022
65°	1833
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P#

CATALOG NUMBER: LD2B20D010 EU2B20WFL559035 2LBDL*H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	149.5	11.0
10°-20°	358.0	26.3
20°-30°	399.3	29.3
30°-40°	279.7	20.5
40°-50°	127.7	9.4
50°-60°	42.7	3.1
60°-70°	4.6	0.3
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	906.8	66.6
0°-40°	1186.5	87.1
0°-60°	1356.9	99.7
0°-90°	1361.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1361.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1649	
5°	1611	149
15°	1285	358
25°	878	399
35°	444	280
45°	159	128
55°	46	43
65°	2	5
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P#

CATALOG NUMBER: LD2B20D010 EU2B20WFL559035 2LBDL*H

CANDELA DISTRIBUTION (FULL):

	0°
0°	1648.9
2.5°	1640.9
5°	1610.8
7.5°	1554.5
10°	1480.2
12.5°	1385.8
15°	1285.4
17.5°	1181.0
20°	1082.6
22.5°	984.1
25°	877.7
27.5°	769.2
30°	656.8
32.5°	546.3
35°	443.9
37.5°	353.5
40°	277.2
42.5°	210.9
45°	158.7
47.5°	118.5
50°	86.4
52.5°	62.3
55°	46.2
57.5°	32.1
60°	18.1
62.5°	6.0
65°	2.0
67.5°	2.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)