

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P#

Luminaire Tested: **LD2B20D010 EU2B20WFL559035 2LBDL*WMH**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P#
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P14805)
Test Lab: INNOVATION CENTER (G1)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD2B20D010 EU2B20WFL559035 2LBDL*WMH
Description: 2000 Lumen, 2inch Portfolio LED Downlight
WIDE FLOOD OPTIC
LENSED SPUN ROUND TRIM WITH WHEAT METALLIC HAZE FINISH
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1349.4 lumens
Efficiency: N/A
Efficacy: 64.6 lumens/watt
Spacing Criteria (0/90/45): 0.78 / 0.78 / 0.83
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 20.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P#

CATALOG NUMBER: LD2B20D010 EU2B20WFL559035 2LBDL*WMH

Luminous Intensity Polar Plot





TEST NUMBER: P#

CATALOG NUMBER: LD2B20D010 EU2B20WFL559035 2LBDL*WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10			50	30	10			50
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111			106	106	106			102
1	113	111	108	106		111	108	106	104		104	103	101			101	99	98			97
2	108	103	99	95		105	101	97	94		98	95	92			95	92	90			92
3	102	95	90	86		100	94	89	86		91	87	84			89	86	83			87
4	97	89	83	79		95	88	83	79		86	81	78			84	80	77			82
5	92	83	77	73		90	82	77	72		80	75	72			79	74	71			77
6	87	78	72	67		85	77	71	67		75	70	67			74	70	66			73
7	82	73	67	63		81	72	67	62		71	66	62			70	65	62			69
8	78	69	63	58		77	68	62	58		67	62	58			66	61	58			65
9	75	65	59	55		73	64	59	55		63	58	54			62	58	54			62
10	71	61	55	51		70	61	55	51		60	55	51			59	54	51			58

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	642646
5°	634991
10°	586914
15°	514416
20°	443945
25°	377897
30°	299312
35°	207728
40°	134956
45°	81237
50°	46943
55°	26270
60°	11465
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P#

CATALOG NUMBER: LD2B20D010 EU2B20WFL559035 2LBDL*WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	151.4	11.2
10°-20°	357.4	26.5
20°-30°	402.3	29.8
30°-40°	277.9	20.6
40°-50°	120.4	8.9
50°-60°	37.3	2.8
60°-70°	2.7	0.2
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	911.1	67.5
0°-40°	1189.0	88.1
0°-60°	1346.7	99.8
0°-90°	1349.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1349.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1659	
5°	1633	151
15°	1283	357
25°	884	402
35°	439	278
45°	148	120
55°	39	37
65°	0	3
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P#

CATALOG NUMBER: LD2B20D010 EU2B20WFL559035 2LBDL*WMH

CANDELA DISTRIBUTION (FULL):

	0°
0°	1659.1
2.5°	1655.4
5°	1633.1
7.5°	1581.2
10°	1492.2
12.5°	1390.3
15°	1282.8
17.5°	1171.6
20°	1077.0
22.5°	982.5
25°	884.2
27.5°	784.1
30°	669.2
32.5°	548.7
35°	439.3
37.5°	344.8
40°	266.9
42.5°	202.1
45°	148.3
47.5°	109.4
50°	77.9
52.5°	55.6
55°	38.9
57.5°	27.8
60°	14.8
62.5°	3.7
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)