

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P497545

Luminaire Tested: **LDA2B158030R60D010 2LBD1MMS**

Issue Date: 3/8/2021

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.



**Test Information**

Test Method: LM-79-08  
Report Number: P497545  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2011-037-53)  
Test Lab: INNOVATION CENTER  
Issue Date: 3/8/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LDA2B158030R60D010 2LBD1MMS  
Description: 1500 LUMEN 2IN ADJUSTABLE LED LUMINAIRE WITH 80 CRI LEDS AND 3000K CCT LEDS  
Light Source: -  
Ballast/Driver: -

Luminaire Equipment: Sample No.    Condition    Description


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1387.3 lumens  
Efficiency: N/A  
Efficacy: 98.4 lumens/watt  
Spacing Criteria (0/90/45): 0.92 / 0.92 / 0.87  
Luminous Opening: Circular (Dia: 0.17' x H: 0')  
CIE Type: Direct

Input Watts (W): 14.1  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P497545  
CATALOG NUMBER: LDA2B158030R60D010 2LBD1MMS

### Luminous Intensity Polar Plot





TEST NUMBER: P497545

CATALOG NUMBER: LDA2B158030R60D010 2LBD1MMS

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	114	111	109	106	111	109	107	105	105	103	102		101	100	99		98	97	96	94
2	108	104	100	96	106	102	98	95	99	96	93		96	93	91		93	91	89	88
3	103	97	92	88	101	96	91	88	93	89	86		91	87	85		88	86	84	82
4	98	91	86	81	96	90	85	81	88	83	80		86	82	79		84	81	78	77
5	93	85	80	75	92	84	79	75	83	78	74		81	77	74		79	76	73	72
6	89	80	74	70	87	79	74	70	78	73	70		77	72	69		75	72	69	67
7	85	76	70	66	83	75	69	66	74	69	65		73	68	65		71	67	64	63
8	81	71	66	62	79	71	65	61	70	65	61		69	64	61		68	64	61	59
9	77	68	62	58	76	67	62	58	66	61	58		65	61	57		64	60	57	56
10	73	64	58	55	72	64	58	54	63	58	54		62	57	54		61	57	54	53

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	830575
5°	788482
10°	771899
15°	747148
20°	683110
25°	606476
30°	453697
35°	256151
40°	96412
45°	43189
50°	21030
55°	4215
60°	1381
65°	817
70°	1010
75°	0
80°	0
85°	0



TEST NUMBER: P497545

CATALOG NUMBER: LDA2B158030R60D010 2LBD1MMS

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	150.7	10.9
10°-20°	406.3	29.3
20°-30°	496.4	35.8
30°-40°	270.7	19.5
40°-50°	54.2	3.9
50°-60°	7.7	0.6
60°-70°	0.9	0.1
70°-80°	0.3	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1053.4	75.9
0°-40°	1324.1	95.4
0°-60°	1386.1	99.9
0°-90°	1387.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1387.3	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1684	
5°	1592	151
15°	1463	406
25°	1114	496
35°	425	271
45°	62	54
55°	5	8
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P497545

CATALOG NUMBER: LDA2B158030R60D010 2LBD1MMS

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	1683.5
1°	1675.8
2°	1661.0
3°	1641.3
4°	1613.2
5°	1592.1
6°	1580.9
7°	1567.5
8°	1557.0
9°	1552.1
10°	1540.8
11°	1528.2
12°	1516.9
13°	1503.6
14°	1483.9
15°	1462.8
16°	1436.1
17°	1398.8
18°	1374.9
19°	1336.3
20°	1301.1
21°	1268.8
22.5°	1214.7
23°	1192.2
24°	1157.7
25°	1114.1
26°	1058.6
27°	1000.3
28°	933.5
29°	870.2
30°	796.4
32.5°	610.8
35°	425.3
37.5°	266.4
40°	149.7
42.5°	93.5
45°	61.9
47.5°	42.2
50°	27.4
52.5°	14.1
55°	4.9
57.5°	2.1
60°	1.4
62.5°	1.4
65°	0.7



TEST NUMBER: P497545

CATALOG NUMBER: LDA2B158030R60D010 2LBD1MMS

**CANDELA DISTRIBUTION (continued):**

	0°
67.5°	0.7
70°	0.7
72.5°	0.7
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)