

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P265095

Luminaire Tested: **LD2B20D010 EU2B2010SP159040 2LBDL*LI**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P265095
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1711-432-2)
Test Lab: INNOVATION CENTER(G3)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD2B20D010 EU2B2010SP159040 2LBDL*LI
Description: 2000 Lumen, 2inch Portfolio LED Downlight
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1497.0 lumens
Efficiency: N/A
Efficacy: 71.6 lumens/watt
Spacing Criteria (0/90/45): 0.31 / 0.31 / 0.32
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 20.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P265095

CATALOG NUMBER: LD2B20D010 EU2B2010SP159040 2LBDL*LI

Luminous Intensity Polar Plot





TEST NUMBER: P265095

CATALOG NUMBER: LD2B20D010 EU2B2010SP159040 2LBDL*LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	115	113	111	110		113	111	110	108		107	106	105		104	103	102		100	99	99
2	112	108	106	103		110	107	104	102		104	102	100		101	99	98		98	97	96
3	109	104	101	98		107	103	100	97		100	98	96		98	96	94		96	94	93
4	105	100	97	94		104	99	96	93		97	95	92		96	93	91		94	92	90
5	103	97	93	91		101	96	93	90		95	92	89		93	91	89		92	90	88
6	100	94	90	88		99	94	90	87		92	89	87		91	88	86		90	88	86
7	98	92	88	85		97	91	88	85		90	87	85		89	86	84		88	86	84
8	95	89	86	83		94	89	85	83		88	85	82		87	84	82		86	84	82
9	93	87	83	81		92	87	83	81		86	83	81		85	82	80		85	82	80
10	91	85	82	79		91	85	81	79		84	81	79		84	81	79		83	80	78

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	5284694
5°	4301215
10°	2323411
15°	926427
20°	371455
25°	177898
30°	92232
35°	48725
40°	27050
45°	16745
50°	11513
55°	7741
60°	5920
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P265095

CATALOG NUMBER: LD2B20D010 EU2B2010SP159040 2LBDL*LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	698.5	46.7
10°-20°	551.1	36.8
20°-30°	162.6	10.9
30°-40°	54.1	3.6
40°-50°	20.3	1.4
50°-60°	9.0	0.6
60°-70°	1.5	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1412.1	94.3
0°-40°	1466.2	97.9
0°-60°	1495.6	99.9
0°-90°	1497.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1497.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	10712	
5°	8685	698
15°	1814	551
25°	327	163
35°	81	54
45°	24	20
55°	9	9
65°	0	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P265095

CATALOG NUMBER: LD2B20D010 EU2B2010SP159040 2LBDL*LI

CANDELA DISTRIBUTION (FULL):

	0°
0°	10711.6
2.5°	10279.9
5°	8685.0
7.5°	6691.4
10°	4637.8
12.5°	2968.0
15°	1813.8
17.5°	1106.2
20°	707.5
22.5°	473.7
25°	326.8
27.5°	230.8
30°	161.9
32.5°	113.9
35°	80.9
37.5°	57.0
40°	42.0
42.5°	33.0
45°	24.0
47.5°	21.0
50°	15.0
52.5°	12.0
55°	9.0
57.5°	9.0
60°	6.0
62.5°	3.0
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)