

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P1179325

Luminaire Tested: LDA2B159024R2040D010 2LBDC1MW

Issue Date: 1/17/2025

Test Information

Test Method: LM-79-2019
Report Number: P1179325
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2206-683-15)
Test Lab: INNOVATION CENTER
Issue Date: 1/17/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LDA2B159024R2040D010 2LBDC1MW
Description: 1500 LUMEN 2IN ADJUSTABLE LED LUMINAIRE WITH 90 CRI LEDS AND 2400K CCT LEDS
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 646.1 lumens
Efficiency: N/A
Efficacy: 45.8 lumens/watt
Spacing Criteria (0/90/45): 0.31 / 0.63 / 0.43
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct

Input Watts (W): 14.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1179325

CATALOG NUMBER: LDA2B159024R2040D010 2LBDC1MW

Luminous Intensity Polar Plot



TEST NUMBER: P1179325

CATALOG NUMBER: LDA2B159024R2040D010 2LBDC1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			0
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	114	112	110	108	112	110	108	106	106	104	103		102	101	100		99	98	97	95
2	110	106	102	99	108	104	101	98	101	98	96		98	96	94		95	94	92	91
3	106	100	96	93	104	99	95	92	96	93	91		94	92	89		92	90	88	87
4	102	95	91	87	100	94	90	87	92	89	86		90	87	85		89	86	84	83
5	98	91	86	83	97	90	86	83	89	85	82		87	84	81		86	83	81	79
6	94	87	83	79	93	87	82	79	85	81	78		84	80	78		83	80	77	76
7	91	84	79	76	90	83	79	75	82	78	75		81	77	75		80	77	74	73
8	88	81	76	73	87	80	76	72	79	75	72		78	75	72		77	74	72	70
9	85	78	73	70	84	77	73	70	76	72	70		76	72	69		75	72	69	68
10	83	75	70	67	82	75	70	67	74	70	67		73	70	67		73	69	67	66

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1130884	1130884	1130884
5°	916651	1029568	1133817
10°	498368	730969	1012466
15°	210793	410196	810432
20°	107630	192894	560359
25°	59608	98693	341534
30°	33384	54804	186287
35°	19333	33186	94920
40°	14362	25117	52554
45°	12629	17024	31118
50°	13355	11206	16579
55°	9634	7827	9032
60°	6216	5526	5526
65°	4903	4903	4903
70°	4039	4039	4039
75°	4003	4003	4003
80°	3978	3978	3978
85°	3962	3962	3962

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°

Vertical Angle: 45°

Luminance: 31118 cd/sqm

TEST NUMBER: P1179325

CATALOG NUMBER: LDA2B159024R2040D010 2LBDC1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	178.6	27.6
10°-20°	252.6	39.1
20°-30°	130.1	20.1
30°-40°	47.9	7.4
40°-50°	21.0	3.3
50°-60°	9.2	1.4
60°-70°	4.1	0.6
70°-80°	2.0	0.3
80°-90°	0.6	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	561.3	86.9
0°-40°	609.2	94.3
0°-60°	639.4	99.0
0°-90°	646.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	646.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2292	2292	2292	2292	2292	
5°	1851	1914	2079	2226	2289	149
15°	413	480	803	1340	1587	126
25°	110	123	181	416	627	53
35°	32	37	55	96	158	22
45°	18	21	24	29	45	15
55°	11	10	9	10	10	10
65°	4	4	4	4	4	4
75°	2	2	2	2	2	2
85°	1	1	1	1	1	1
90°	0	0	0	0	0	

TEST NUMBER: P1179325

CATALOG NUMBER: LDA2B159024R2040D010 2LBDC1MW

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2292.2	2292.2	2292.2	2292.2	2292.2
2.5°	2161.1	2186.9	2235.0	2281.1	2299.9
5°	1850.9	1913.7	2078.9	2226.0	2289.4
7.5°	1433.3	1536.5	1804.2	2079.6	2192.5
10°	994.8	1099.4	1459.1	1855.1	2021.0
12.5°	634.4	736.2	1124.5	1606.2	1821.6
15°	412.7	479.6	803.1	1339.9	1586.7
17.5°	286.5	333.9	546.6	1057.6	1326.7
20°	205.0	238.4	367.4	806.6	1067.3
22.5°	148.5	171.5	255.2	589.1	829.6
25°	109.5	122.7	181.3	416.2	627.4
27.5°	80.9	89.2	131.1	287.2	458.7
30°	58.6	65.5	96.2	197.3	327.0
32.5°	42.5	48.8	71.8	136.6	228.0
35°	32.1	36.9	55.1	96.2	157.6
37.5°	26.5	29.3	45.3	69.7	111.5
40°	22.3	25.1	39.0	51.6	81.6
42.5°	19.5	23.0	32.1	38.3	61.3
45°	18.1	20.9	24.4	29.3	44.6
47.5°	18.1	17.4	18.8	22.3	31.4
50°	17.4	14.6	14.6	17.4	21.6
52.5°	14.6	11.9	11.9	12.5	14.6
55°	11.2	9.8	9.1	9.8	10.5
57.5°	8.4	8.4	7.7	7.0	7.7
60°	6.3	6.3	5.6	5.6	5.6
62.5°	4.9	4.9	4.9	4.2	4.9
65°	4.2	4.2	4.2	3.5	4.2
67.5°	3.5	3.5	2.8	3.5	3.5
70°	2.8	2.8	2.8	2.8	2.8
72.5°	2.1	2.1	2.1	2.1	2.1
75°	2.1	2.1	2.1	2.1	2.1
77.5°	1.4	1.4	1.4	1.4	1.4
80°	1.4	1.4	1.4	1.4	1.4
82.5°	0.7	0.7	0.7	0.7	0.7
85°	0.7	0.7	0.7	0.7	0.7
87.5°	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)