

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P1179174

Luminaire Tested: LDA2B158030R2050D010 2LBD1GPH

Issue Date: 1/17/2025

**Test Information**

Test Method: LM-79-2019  
Report Number: P1179174  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2206-683-20)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/17/2025  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PORTFOLIO  
Catalog Number: LDA2B158030R2050D010 2LBD1GPH  
Description: 1500 LUMEN 2IN ADJUSTABLE LED LUMINAIRE WITH 80 CRI LEDS AND 3000K CCT LEDS  
Light Source: -  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 1222.3 lumens  
Efficiency: N/A  
Efficacy: 86.7 lumens/watt  
Spacing Criteria (0/90/45): 0.33 / 0.8 / 0.47  
Luminous Opening: Circular (Dia: 0.17' x H: 0')  
CIE Type: Direct

Input Watts (W): 14.1  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1179174

CATALOG NUMBER: LDA2B158030R2050D010 2LBD1GPH

### Luminous Intensity Polar Plot



TEST NUMBER: P1179174

CATALOG NUMBER: LDA2B158030R2050D010 2LBD1GPH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |     |     |     |     |     |     |     |  |     |     |     |  |     |     |     |     |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|--|-----|-----|-----|--|-----|-----|-----|-----|
| RF  | 20  |     |     |     | 20  |     |     |     | 20  |     |     |  | 20  |     |     |  | 20  |     |     |     |
| RC  | 80  |     |     |     | 70  |     |     |     | 50  |     |     |  | 30  |     |     |  | 10  |     |     | 0   |
| RW  | 70  | 50  | 30  | 10  | 70  | 50  | 30  | 10  | 50  | 30  | 10  |  | 50  | 30  | 10  |  | 50  | 30  | 10  | 0   |
| RCR |     |     |     |     |     |     |     |     |     |     |     |  |     |     |     |  |     |     |     |     |
| 0   | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 |  | 106 | 106 | 106 |  | 102 | 102 | 102 | 100 |
| 1   | 114 | 112 | 109 | 107 | 112 | 109 | 107 | 106 | 105 | 104 | 102 |  | 102 | 100 | 99  |  | 98  | 97  | 96  | 95  |
| 2   | 109 | 105 | 101 | 98  | 107 | 103 | 100 | 97  | 100 | 97  | 95  |  | 97  | 95  | 93  |  | 94  | 93  | 91  | 90  |
| 3   | 105 | 99  | 95  | 91  | 103 | 98  | 94  | 90  | 95  | 92  | 89  |  | 93  | 90  | 88  |  | 90  | 88  | 86  | 85  |
| 4   | 100 | 94  | 89  | 85  | 99  | 93  | 88  | 85  | 91  | 87  | 84  |  | 89  | 85  | 83  |  | 87  | 84  | 82  | 80  |
| 5   | 96  | 89  | 84  | 80  | 95  | 88  | 83  | 80  | 86  | 82  | 79  |  | 85  | 81  | 78  |  | 83  | 80  | 78  | 76  |
| 6   | 92  | 85  | 80  | 76  | 91  | 84  | 79  | 76  | 83  | 78  | 75  |  | 81  | 77  | 75  |  | 80  | 77  | 74  | 73  |
| 7   | 89  | 81  | 76  | 72  | 88  | 80  | 75  | 72  | 79  | 75  | 71  |  | 78  | 74  | 71  |  | 77  | 73  | 71  | 70  |
| 8   | 85  | 77  | 72  | 69  | 84  | 77  | 72  | 69  | 76  | 71  | 68  |  | 75  | 71  | 68  |  | 74  | 70  | 68  | 67  |
| 9   | 82  | 74  | 69  | 66  | 81  | 74  | 69  | 66  | 73  | 68  | 65  |  | 72  | 68  | 65  |  | 71  | 68  | 65  | 64  |
| 10  | 79  | 71  | 66  | 63  | 79  | 71  | 66  | 63  | 70  | 66  | 63  |  | 69  | 65  | 62  |  | 69  | 65  | 62  | 61  |

**AVERAGE LUMINANCE (cd/sqm):**

|     | 0°      | 45°     | 90°     |
|-----|---------|---------|---------|
| 0°  | 1677627 | 1677627 | 1677627 |
| 5°  | 1379261 | 1521793 | 1688245 |
| 10° | 800604  | 1124533 | 1645946 |
| 15° | 373012  | 700362  | 1499966 |
| 20° | 196569  | 369250  | 1232863 |
| 25° | 108818  | 199945  | 909306  |
| 30° | 63805   | 117127  | 588086  |
| 35° | 41016   | 78598   | 348421  |
| 40° | 31944   | 52940   | 193598  |
| 45° | 27699   | 31676   | 86099   |
| 50° | 25022   | 21798   | 31546   |
| 55° | 17117   | 15827   | 14623   |
| 60° | 12630   | 11150   | 11150   |
| 65° | 9923    | 8288    | 9923    |
| 70° | 8222    | 8222    | 8222    |
| 75° | 8197    | 8197    | 8197    |
| 80° | 7955    | 7955    | 7955    |
| 85° | 7925    | 7925    | 7925    |

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 90°

Vertical Angle: 45°

Luminance: 86099 cd/sqm

TEST NUMBER: P1179174

CATALOG NUMBER: LDA2B158030R2050D010 2LBD1GPH

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 270.7  | 22.2      |
| 10°-20°   | 443.3  | 36.3      |
| 20°-30°   | 295.7  | 24.2      |
| 30°-40°   | 133.3  | 10.9      |
| 40°-50°   | 48.8   | 4.0       |
| 50°-60°   | 17.1   | 1.4       |
| 60°-70°   | 8.0    | 0.7       |
| 70°-80°   | 4.2    | 0.3       |
| 80°-90°   | 1.1    | 0.1       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| 0°-30°    | 1009.8 | 82.6      |
| 0°-40°    | 1143.1 | 93.5      |
| 0°-60°    | 1209.0 | 98.9      |
| 0°-90°    | 1222.3 | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 1222.3 | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°   | 22.5° | 45°  | 67.5° | 90°  | Flux |
|-----|------|-------|------|-------|------|------|
| 0°  | 3400 | 3400  | 3400 | 3400  | 3400 |      |
| 5°  | 2785 | 2872  | 3073 | 3297  | 3409 | 227  |
| 15° | 730  | 858   | 1371 | 2317  | 2937 | 219  |
| 25° | 200  | 233   | 367  | 1001  | 1670 | 97   |
| 35° | 68   | 77    | 130  | 282   | 578  | 45   |
| 45° | 40   | 40    | 45   | 71    | 123  | 31   |
| 55° | 20   | 18    | 18   | 16    | 17   | 19   |
| 65° | 8    | 8     | 7    | 7     | 8    | 9    |
| 75° | 4    | 4     | 4    | 4     | 4    | 4    |
| 85° | 1    | 1     | 1    | 1     | 1    | 1    |
| 90° | 0    | 0     | 0    | 0     | 0    |      |

TEST NUMBER: P1179174

CATALOG NUMBER: LDA2B158030R2050D010 2LBD1GPH

**CANDELA DISTRIBUTION (FULL):**

|       | 0°     | 22.5°  | 45°    | 67.5°  | 90°    |
|-------|--------|--------|--------|--------|--------|
| 0°    | 3400.4 | 3400.4 | 3400.4 | 3400.4 | 3400.4 |
| 2.5°  | 3228.8 | 3262.8 | 3302.6 | 3343.7 | 3376.3 |
| 5°    | 2785.0 | 2871.5 | 3072.8 | 3296.9 | 3408.9 |
| 7.5°  | 2202.2 | 2329.8 | 2721.2 | 3163.6 | 3400.4 |
| 10°   | 1598.1 | 1761.2 | 2244.7 | 2932.4 | 3285.5 |
| 12.5° | 1099.0 | 1252.1 | 1800.9 | 2640.3 | 3133.8 |
| 15°   | 730.3  | 857.9  | 1371.2 | 2317.0 | 2936.7 |
| 17.5° | 514.7  | 601.2  | 996.9  | 1963.9 | 2682.9 |
| 20°   | 374.4  | 432.5  | 703.3  | 1618.0 | 2348.2 |
| 22.5° | 272.3  | 316.2  | 500.6  | 1293.2 | 2009.3 |
| 25°   | 199.9  | 232.6  | 367.3  | 1001.1 | 1670.4 |
| 27.5° | 148.9  | 174.4  | 275.1  | 760.1  | 1331.5 |
| 30°   | 112.0  | 133.3  | 205.6  | 560.1  | 1032.3 |
| 32.5° | 86.5   | 100.7  | 157.4  | 399.9  | 781.3  |
| 35°   | 68.1   | 76.6   | 130.5  | 282.2  | 578.5  |
| 37.5° | 56.7   | 62.4   | 107.8  | 197.1  | 424.0  |
| 40°   | 49.6   | 53.9   | 82.2   | 140.4  | 300.6  |
| 42.5° | 44.0   | 46.8   | 59.6   | 100.7  | 195.7  |
| 45°   | 39.7   | 39.7   | 45.4   | 70.9   | 123.4  |
| 47.5° | 36.9   | 32.6   | 35.5   | 49.6   | 72.3   |
| 50°   | 32.6   | 26.9   | 28.4   | 34.0   | 41.1   |
| 52.5° | 25.5   | 22.7   | 22.7   | 22.7   | 24.1   |
| 55°   | 19.9   | 18.4   | 18.4   | 15.6   | 17.0   |
| 57.5° | 15.6   | 15.6   | 14.2   | 12.8   | 14.2   |
| 60°   | 12.8   | 12.8   | 11.3   | 9.9    | 11.3   |
| 62.5° | 9.9    | 9.9    | 8.5    | 8.5    | 9.9    |
| 65°   | 8.5    | 8.5    | 7.1    | 7.1    | 8.5    |
| 67.5° | 7.1    | 7.1    | 7.1    | 5.7    | 7.1    |
| 70°   | 5.7    | 5.7    | 5.7    | 5.7    | 5.7    |
| 72.5° | 4.3    | 4.3    | 5.7    | 4.3    | 4.3    |
| 75°   | 4.3    | 4.3    | 4.3    | 4.3    | 4.3    |
| 77.5° | 2.8    | 2.8    | 2.8    | 2.8    | 2.8    |
| 80°   | 2.8    | 2.8    | 2.8    | 2.8    | 2.8    |
| 82.5° | 1.4    | 1.4    | 1.4    | 1.4    | 1.4    |
| 85°   | 1.4    | 1.4    | 1.4    | 1.4    | 1.4    |
| 87.5° | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 90°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |

(END OF REPORT)