

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P1179959

Luminaire Tested: LDA2B209035R2050D010 2LBDC1MW

Issue Date: 1/17/2025

Test Information

Test Method: LM-79-2019
Report Number: P1179959
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2206-683-20)
Test Lab: INNOVATION CENTER
Issue Date: 1/17/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LDA2B209035R2050D010 2LBDC1MW
Description: 2000 LUMEN 2IN ADJUSTABLE LED LUMINAIRE WITH 90 CRI LEDS AND 3500K CCT LEDS
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 966.6 lumens
Efficiency: N/A
Efficacy: 46.9 lumens/watt
Spacing Criteria (0/90/45): 0.33 / 0.8 / 0.47
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct

Input Watts (W): 20.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1179959

CATALOG NUMBER: LDA2B209035R2050D010 2LBDC1MW

Luminous Intensity Polar Plot



TEST NUMBER: P1179959

CATALOG NUMBER: LDA2B209035R2050D010 2LBDC1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			0
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	114	112	109	107	112	109	107	106	105	104	102		102	100	99		98	97	96	95
2	109	105	101	98	107	103	100	97	100	97	95		97	95	93		94	93	91	90
3	105	99	95	91	103	98	94	90	95	92	89		93	90	88		90	88	86	85
4	100	94	89	85	99	93	88	85	91	87	84		89	85	83		87	84	82	80
5	96	89	84	80	95	88	83	80	86	82	79		85	81	78		83	80	78	76
6	92	85	80	76	91	84	79	76	83	78	75		81	77	75		80	77	74	73
7	89	81	76	72	88	80	75	72	79	75	71		78	74	71		77	73	71	70
8	85	77	72	69	84	77	72	69	76	71	68		75	71	68		74	70	68	67
9	82	74	69	66	81	74	69	66	73	68	65		72	68	65		71	68	65	64
10	79	71	66	63	79	71	66	63	70	66	63		69	65	62		69	65	62	61

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1326749	1326749	1326749
5°	1090780	1203498	1335135
10°	633179	889327	1301727
15°	294967	553874	1186253
20°	155460	292019	975023
25°	86064	158138	719160
30°	50474	92631	465091
35°	32403	62156	275545
40°	25311	41862	153088
45°	21908	25048	68097
50°	19802	17193	24945
55°	13504	12558	11612
60°	9966	8881	8881
65°	7822	6537	7822
70°	6491	6491	6491
75°	6481	6481	6481
80°	6251	6251	6251
85°	6227	6227	6227

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°

Vertical Angle: 45°

Luminance: 68097 cd/sqm

TEST NUMBER: P1179959

CATALOG NUMBER: LDA2B209035R2050D010 2LBDC1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	214.1	22.2
10°-20°	350.6	36.3
20°-30°	233.9	24.2
30°-40°	105.4	10.9
40°-50°	38.6	4.0
50°-60°	13.5	1.4
60°-70°	6.3	0.7
70°-80°	3.3	0.3
80°-90°	0.9	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	798.6	82.6
0°-40°	904.0	93.5
0°-60°	956.1	98.9
0°-90°	966.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	966.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2689	2689	2689	2689	2689	
5°	2202	2271	2430	2607	2696	180
15°	578	678	1084	1832	2322	173
25°	158	184	290	792	1321	76
35°	54	61	103	223	458	36
45°	31	31	36	56	98	25
55°	16	15	15	12	14	15
65°	7	7	6	6	7	7
75°	3	3	3	3	3	3
85°	1	1	1	1	1	1
90°	0	0	0	0	0	

TEST NUMBER: P1179959

CATALOG NUMBER: LDA2B209035R2050D010 2LBDC1MW

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2689.2	2689.2	2689.2	2689.2	2689.2
2.5°	2553.5	2580.4	2611.8	2644.3	2670.1
5°	2202.5	2270.9	2430.1	2607.3	2695.9
7.5°	1741.6	1842.5	2152.0	2501.9	2689.2
10°	1263.9	1392.8	1775.2	2319.1	2598.4
12.5°	869.1	990.2	1424.2	2088.1	2478.4
15°	577.5	678.5	1084.4	1832.4	2322.5
17.5°	407.1	475.5	788.4	1553.2	2121.8
20°	296.1	342.0	556.2	1279.6	1857.1
22.5°	215.3	250.1	395.9	1022.7	1589.1
25°	158.1	183.9	290.5	791.7	1321.1
27.5°	117.8	137.9	217.6	601.1	1053.0
30°	88.6	105.4	162.6	443.0	816.4
32.5°	68.4	79.6	124.5	316.2	617.9
35°	53.8	60.6	103.2	223.2	457.5
37.5°	44.9	49.3	85.2	155.9	335.3
40°	39.3	42.6	65.0	111.0	237.7
42.5°	34.8	37.0	47.1	79.6	154.8
45°	31.4	31.4	35.9	56.1	97.6
47.5°	29.2	25.8	28.0	39.3	57.2
50°	25.8	21.3	22.4	26.9	32.5
52.5°	20.2	17.9	17.9	17.9	19.1
55°	15.7	14.6	14.6	12.3	13.5
57.5°	12.3	12.3	11.2	10.1	11.2
60°	10.1	10.1	9.0	7.9	9.0
62.5°	7.9	7.9	6.7	6.7	7.9
65°	6.7	6.7	5.6	5.6	6.7
67.5°	5.6	5.6	5.6	4.5	5.6
70°	4.5	4.5	4.5	4.5	4.5
72.5°	3.4	3.4	4.5	3.4	3.4
75°	3.4	3.4	3.4	3.4	3.4
77.5°	2.2	2.2	2.2	2.2	2.2
80°	2.2	2.2	2.2	2.2	2.2
82.5°	1.1	1.1	1.1	1.1	1.1
85°	1.1	1.1	1.1	1.1	1.1
87.5°	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)