

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P#

Luminaire Tested: LDRT3D13R129030DE010 3LPHUSR1MB

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P#
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2501-338-24)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: LDRT3D13R129030DE010 3LPHUSR1MB
Description: 3in Adjustable LED luminaire with, R12 optic, 3000K CCT AND, 90CRI , 3LPHUSR1MB TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1124.0 lumens
Efficiency: N/A
Efficacy: 72.5 lumens/watt
Spacing Criteria (0/90/45): 0.22 / 0.22 / 0.22
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 15.5
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P#

CATALOG NUMBER: LDRT3D13R129030DE010 3LPHUSR1MB

Luminous Intensity Polar Plot



TEST NUMBER: P#

CATALOG NUMBER: LDRT3D13R129030DE010 3LPHUSR1MB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0			
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	116	114	113	111	114	112	111	109	108	107	106	104	104	103	101	101	100	98			
2	113	110	108	106	111	108	106	104	105	104	102	103	101	100	100	99	98	97			
3	110	107	104	102	109	105	103	101	103	101	99	101	99	98	99	98	96	95			
4	108	104	101	98	107	103	100	98	101	99	97	99	97	96	98	96	95	94			
5	106	102	98	96	105	101	98	96	99	97	95	98	96	94	97	95	93	92			
6	104	99	96	94	103	99	96	94	98	95	93	96	94	93	95	93	92	91			
7	102	98	94	92	101	97	94	92	96	93	92	95	93	91	94	92	91	90			
8	101	96	93	91	100	95	93	90	95	92	90	94	92	90	93	91	90	89			
9	99	94	91	89	98	94	91	89	93	91	89	93	90	89	92	90	88	88			
10	98	93	90	88	97	93	90	88	92	90	88	91	89	88	91	89	87	87			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	3631113
5°	2346175
10°	661978
15°	187175
20°	78267
25°	34647
30°	17699
35°	9342
40°	4008
45°	1085
50°	1194
55°	0
60°	0
65°	0
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 50°

Luminance: 1194 cd/sqm

TEST NUMBER: P#

CATALOG NUMBER: LDRT3D13R129030DE010 3LPUSR1MB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	751.0	66.8
10°-20°	272.5	24.2
20°-30°	73.0	6.5
30°-40°	22.9	2.0
40°-50°	4.3	0.4
50°-60°	0.4	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1096.4	97.5
0°-40°	1119.3	99.6
0°-60°	1124.0	100.0
0°-90°	1124.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1124.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	16559	
5°	10659	751
15°	824	272
25°	143	73
35°	35	23
45°	4	4
55°	0	0
65°	0	0
75°	0	0
85°	0	0
90°	0	

TEST NUMBER: P#

CATALOG NUMBER: LDRT3D13R129030DE010 3LPHUSR1MB

CANDELA DISTRIBUTION (FULL):

0°	
0°	16559.2
1°	16279.7
2°	15493.7
3°	14148.7
4°	12478.8
5°	10658.7
6°	8761.7
7°	7063.9
8°	5435.9
9°	4045.5
10°	2973.0
11°	2190.4
12°	1648.9
13°	1278.6
14°	1013.1
15°	824.5
17.5°	524.0
20°	335.4
22.5°	216.6
25°	143.2
27.5°	97.8
30°	69.9
32.5°	48.9
35°	34.9
37.5°	24.5
40°	14.0
42.5°	7.0
45°	3.5
47.5°	3.5
50°	3.5
52.5°	0.0
55°	0.0
57.5°	0.0
60°	0.0
62.5°	0.0
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0



TEST NUMBER: P#
CATALOG NUMBER: LDRT3D13R129030DE010 3LPHUSR1MB

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)