

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P1307332

Luminaire Tested: LDSQA3D17R359024DE010 3LSQPHR1MMS

Issue Date: 1/29/2026

**Test Information**

Test Method: LM-79-2019  
Report Number: P1307332  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2510-583-5)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/29/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PORTFOLIO  
Catalog Number: LDSQA3D17R359024DE010 3LSQPHR1MMS  
Description: 3in Adjustable LED luminaire with, R35 optic, 2400K CCT AND, 90CRI , 3LSQPHR1MMS TRIM  
Light Source: -  
Ballast/Driver: -


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1318.0 lumens  
Efficiency: N/A  
Efficacy: 62.2 lumens/watt  
Spacing Criteria (0/90/45): 0.57 / 0.56 / 0.51  
Luminous Opening: Rectangular (W 0.25' x L: 0.25' x H: 0')  
CIE Type: Direct

Input Watts (W): 21.2  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1307332  
CATALOG NUMBER: LDSQA3D17R359024DE010 3LSQPHR1MMS

### Luminous Intensity Polar Plot





TEST NUMBER: P1307332  
 CATALOG NUMBER: LDSQA3D17R359024DE010 3LSQPHR1MMS

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10		0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	99	98
1	115	113	111	109	113	111	109	108	107	106	104	103	102	101	100	99	98	97	96	95
2	111	108	105	102	109	106	103	101	103	101	99	100	98	97	97	96	95	94	93	92
3	108	103	100	97	106	102	99	96	99	97	94	97	95	93	95	93	92	91	90	89
4	104	99	95	92	103	98	94	92	96	93	91	94	92	90	93	90	89	88	87	86
5	101	95	91	88	100	95	91	88	93	90	87	92	89	87	90	88	86	85	84	83
6	98	92	88	85	97	91	88	85	90	87	84	89	86	84	88	85	83	82	81	80
7	96	89	85	82	94	89	85	82	87	84	81	86	83	81	85	83	81	80	79	78
8	93	86	82	79	92	86	82	79	85	81	79	84	81	79	83	80	78	77	76	75
9	90	84	80	77	89	83	79	77	82	79	76	82	79	76	81	78	76	75	74	73
10	88	81	77	75	87	81	77	74	80	77	74	80	76	74	79	76	74	73	72	71

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	747860	747860	747860
5°	735001	733446	731872
10°	673618	653367	637488
15°	482350	466962	461293
20°	223669	231367	239486
25°	53074	75498	78747
30°	15571	17838	20085
35°	3574	5719	5256
40°	764	1529	1012
45°	268	268	268
50°	295	0	295
55°	0	0	0
60°	0	0	0
65°	0	0	0
70°	0	0	0
75°	0	0	0
80°	0	0	0
85°	0	0	0

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 52.5°  
 Luminance: 311 cd/sqm



TEST NUMBER: P1307332

CATALOG NUMBER: LDSQA3D17R359024DE010 3LSQPHR1MMS

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	389.9	29.6
10°-20°	696.9	52.9
20°-30°	209.7	15.9
30°-40°	20.0	1.5
40°-50°	1.4	0.1
50°-60°	0.1	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1296.5	98.4
0°-40°	1316.5	99.9
0°-60°	1318.0	100.0
0°-90°	1318.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1318.0	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	4342	4342	4342	4342	4342	
5°	4252	4250	4242	4237	4233	394
15°	2705	2685	2619	2608	2587	715
25°	279	308	397	414	414	180
35°	17	23	27	30	25	16
45°	1	1	1	1	1	1
55°	0	0	0	0	0	0
65°	0	0	0	0	0	0
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	0	0	0	0	0	0



TEST NUMBER: P1307332  
 CATALOG NUMBER: LDSQA3D17R359024DE010 3LSQPHR1MMS

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	4342.4	4342.4	4342.4	4342.4	4342.4
1°	4340.1	4340.1	4337.8	4337.8	4333.3
2°	4329.9	4331.0	4326.5	4325.3	4321.9
3°	4314.0	4310.6	4310.6	4308.3	4306.0
4°	4289.0	4282.2	4279.9	4281.1	4276.5
5°	4251.5	4250.4	4242.5	4236.8	4233.4
6°	4210.7	4202.7	4185.7	4170.9	4167.5
7°	4149.4	4132.3	4117.6	4086.9	4082.4
8°	4074.4	4047.2	4015.4	3972.3	3970.0
9°	3982.5	3938.2	3893.9	3836.0	3815.6
10°	3851.9	3811.1	3736.1	3685.0	3645.3
11°	3689.6	3638.5	3551.1	3489.8	3456.9
12°	3505.7	3458.0	3355.8	3300.2	3253.6
13°	3269.5	3229.8	3134.4	3073.1	3036.8
14°	2995.9	2966.4	2875.6	2848.4	2835.9
15°	2705.3	2684.9	2619.0	2607.7	2587.2
17.5°	1991.2	1957.2	1919.7	1926.5	1933.3
20°	1220.4	1268.1	1262.4	1287.4	1306.7
22.5°	608.5	669.8	741.3	784.5	806.0
25°	279.3	307.7	397.3	414.4	414.4
27.5°	140.8	147.6	187.3	190.7	199.8
30°	78.3	84.0	89.7	99.9	101.0
32.5°	39.7	46.5	48.8	54.5	52.2
35°	17.0	22.7	27.2	29.5	25.0
37.5°	7.9	10.2	14.8	13.6	10.2
40°	3.4	4.5	6.8	5.7	4.5
42.5°	2.3	2.3	3.4	2.3	2.3
45°	1.1	1.1	1.1	1.1	1.1
47.5°	1.1	1.1	0.0	1.1	1.1
50°	1.1	0.0	0.0	0.0	1.1
52.5°	1.1	0.0	0.0	0.0	1.1
55°	0.0	0.0	0.0	0.0	0.0
57.5°	0.0	0.0	0.0	0.0	0.0
60°	0.0	0.0	0.0	0.0	0.0
62.5°	0.0	0.0	0.0	0.0	0.0
65°	0.0	0.0	0.0	0.0	0.0
67.5°	0.0	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P1307332  
CATALOG NUMBER: LDSQA3D17R359024DE010 3LSQPHR1MMS

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)