

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P#

Luminaire Tested: **LSSQWM2B20WFL559727D010 2LBDL*H**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P#
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P14807)
Test Lab: INNOVATION CENTER (G1)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSSQWM2B20WFL559727D010 2LBDL*H
Description: 2000 Lumen, 2inch Portfolio LED Cylinder
WIDE FLOOD OPTIC
LENSED SPUN ROUND TRIM WITH HAZE FINISH
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1128.9 lumens
Efficiency: N/A
Efficacy: 54.0 lumens/watt
Spacing Criteria (0/90/45): 0.79 / 0.79 / 0.83
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 20.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P#

CATALOG NUMBER: LSSQWM2B20WFL559727D010 2LBDL*H

Luminous Intensity Polar Plot





TEST NUMBER: P#

CATALOG NUMBER: LSSQWM2B20WFL559727D010 2LBDL*H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	113	111	108	106		111	108	106	104		104	102	101		101	99	98		97	96	95
2	108	102	98	95		105	101	97	94		98	94	92		95	92	90		92	90	88
3	102	95	90	86		100	94	89	85		91	87	84		89	85	83		86	84	81
4	96	89	83	79		95	87	82	78		85	81	77		83	79	76		81	78	75
5	91	83	77	72		90	82	76	72		80	75	71		78	74	71		77	73	70
6	87	77	71	67		85	77	71	67		75	70	66		74	69	66		72	68	65
7	82	73	66	62		81	72	66	62		71	65	62		69	65	61		68	64	61
8	78	68	62	58		77	68	62	58		67	61	57		66	61	57		65	60	57
9	74	64	58	54		73	64	58	54		63	58	54		62	57	54		61	57	54
10	71	61	55	51		70	60	55	51		60	54	51		59	54	51		58	54	50

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	529579
5°	519315
10°	482763
15°	427397
20°	369995
25°	311054
30°	243582
35°	174013
40°	116197
45°	72089
50°	43146
55°	25865
60°	11620
65°	1558
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P#

CATALOG NUMBER: LSSQWM2B20WFL559727D010 2LBDL*H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	124.0	11.0
10°-20°	296.8	26.3
20°-30°	331.1	29.3
30°-40°	231.9	20.5
40°-50°	105.9	9.4
50°-60°	35.4	3.1
60°-70°	3.9	0.3
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	751.9	66.6
0°-40°	983.8	87.1
0°-60°	1125.1	99.7
0°-90°	1128.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1128.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1367	
5°	1336	124
15°	1066	297
25°	728	331
35°	368	232
45°	132	106
55°	38	35
65°	2	4
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P#

CATALOG NUMBER: LSSQWM2B20WFL559727D010 2LBDL*H

CANDELA DISTRIBUTION (FULL):

	0°
0°	1367.2
2.5°	1360.6
5°	1335.6
7.5°	1289.0
10°	1227.4
12.5°	1149.1
15°	1065.8
17.5°	979.2
20°	897.6
22.5°	816.0
25°	727.8
27.5°	637.8
30°	544.6
32.5°	453.0
35°	368.0
37.5°	293.1
40°	229.8
42.5°	174.9
45°	131.6
47.5°	98.3
50°	71.6
52.5°	51.6
55°	38.3
57.5°	26.6
60°	15.0
62.5°	5.0
65°	1.7
67.5°	1.7
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)