

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P#

Luminaire Tested: LDRT3D02R089035DE010 3LCBUSR1MW

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P#
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2408-211-1)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: LDRT3D02R089035DE010 3LCBUSR1MW
Description: 3in Adjustable LED luminaire with, R08 optic, 3500K CCT AND, 90CRI , 3LCBUSR1MW TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 254.0 lumens
Efficiency: N/A
Efficacy: 51.8 lumens/watt
Spacing Criteria (0/90/45): 0.16 / 0.16 / 0.16
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 4.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P#
CATALOG NUMBER: LDRT3D02R089035DE010 3LCBUSR1MW

Luminous Intensity Polar Plot





TEST NUMBER: P#

CATALOG NUMBER: LDRT3D02R089035DE010 3LCBUSR1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10		0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102		100
1	116	114	113	111	114	112	111	110	108	107	106		105	104	103		101	101	100		99
2	113	111	108	106	111	109	107	105	106	104	103		103	102	101		101	100	99		97
3	111	108	105	103	109	106	104	102	104	102	100		102	100	99		100	98	97		96
4	109	105	102	100	108	104	101	99	102	100	98		100	99	97		99	97	96		95
5	107	103	100	98	106	102	99	97	101	98	97		99	97	96		98	96	95		94
6	105	101	98	96	104	100	98	96	99	97	95		98	96	95		97	95	94		93
7	104	100	97	95	103	99	96	94	98	96	94		97	95	94		96	94	93		92
8	103	98	95	93	102	98	95	93	97	95	93		96	94	93		95	94	92		92
9	101	97	94	92	101	97	94	92	96	94	92		95	93	92		95	93	92		91
10	100	96	93	91	100	96	93	91	95	93	91		94	92	91		94	92	91		90

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1440608
5°	600725
10°	96680
15°	27696
20°	9334
25°	4113
30°	2279
35°	1606
40°	1431
45°	930
50°	682
55°	382
60°	439
65°	519
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 930 cd/sqm

TEST NUMBER: P#

CATALOG NUMBER: LDRT3D02R089035DE010 3LCBUSR1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	195.9	77.1
10°-20°	41.0	16.1
20°-30°	8.9	3.5
30°-40°	3.9	1.5
40°-50°	2.4	0.9
50°-60°	1.0	0.4
60°-70°	0.9	0.3
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	245.9	96.8
0°-40°	249.7	98.3
0°-60°	253.1	99.7
0°-90°	254.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	254.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	6570	
5°	2729	196
15°	122	41
25°	17	9
35°	6	4
45°	3	2
55°	1	1
65°	1	1
75°	0	0
85°	0	0
90°	0	

TEST NUMBER: P#

CATALOG NUMBER: LDRT3D02R089035DE010 3LCBUSR1MW

CANDELA DISTRIBUTION (FULL):

0°	
0°	6569.7
2.5°	5491.2
5°	2729.1
7.5°	1017.4
10°	434.2
12.5°	224.1
15°	122.0
17.5°	69.0
20°	40.0
22.5°	26.0
25°	17.0
27.5°	13.0
30°	9.0
32.5°	7.0
35°	6.0
37.5°	5.0
40°	5.0
42.5°	4.0
45°	3.0
47.5°	2.0
50°	2.0
52.5°	1.0
55°	1.0
57.5°	1.0
60°	1.0
62.5°	1.0
65°	1.0
67.5°	1.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)