

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P1307255

Luminaire Tested: LDSQA3D17R129024DE010 3LSQPHRLD1MW

Issue Date: 1/30/2026

**Test Information**

Test Method: LM-79-2019  
Report Number: P1307255  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2501-338-24)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PORTFOLIO  
Catalog Number: LDSQA3D17R129024DE010 3LSQPHRLD1MW  
Description: 3in Adjustable LED luminaire with, R12 optic, 2400K CCT AND, 90CRI , 3LSQPHRLD1MW TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 1202.0 lumens  
Efficiency: N/A  
Efficacy: 52.5 lumens/watt  
Spacing Criteria (0/90/45): 0.22 / 0.22 / 0.22  
Luminous Opening: Rectangular (W 0.25' x L: 0.25' x H: 0')  
CIE Type: Direct

Input Watts (W): 22.9  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1307255

CATALOG NUMBER: LDSQA3D17R129024DE010 3LSQPHRLD1MW

### Luminous Intensity Polar Plot





TEST NUMBER: P1307255

CATALOG NUMBER: LDSQA3D17R129024DE010 3LSQPHRLD1MW

### COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

|     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |  |  |   |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|--|--|---|
| RF  | 20  |     |     |     | 20  |     |     |     | 20  |     |     |     | 20  |     |     |     | 20  |     |  |  |   |
| RC  | 80  |     |     |     | 70  |     |     |     | 50  |     |     |     | 30  |     |     |     | 10  |     |  |  | 0 |
| RW  | 70  | 50  | 30  | 10  | 70  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 0   |  |  |   |
| RCR |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |  |  |   |
| 0   | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | 106 | 106 | 106 | 102 | 102 | 102 | 100 |  |  |   |
| 1   | 116 | 114 | 113 | 111 | 114 | 112 | 111 | 109 | 108 | 107 | 106 | 104 | 104 | 103 | 101 | 101 | 100 | 98  |  |  |   |
| 2   | 113 | 110 | 108 | 106 | 111 | 108 | 106 | 104 | 105 | 104 | 102 | 103 | 101 | 100 | 100 | 99  | 98  | 97  |  |  |   |
| 3   | 110 | 107 | 104 | 102 | 109 | 105 | 103 | 101 | 103 | 101 | 99  | 101 | 99  | 98  | 99  | 98  | 96  | 95  |  |  |   |
| 4   | 108 | 104 | 101 | 98  | 107 | 103 | 100 | 98  | 101 | 99  | 97  | 99  | 97  | 96  | 98  | 96  | 95  | 94  |  |  |   |
| 5   | 106 | 102 | 98  | 96  | 105 | 101 | 98  | 96  | 99  | 97  | 95  | 98  | 96  | 94  | 97  | 95  | 93  | 92  |  |  |   |
| 6   | 104 | 99  | 96  | 94  | 103 | 99  | 96  | 94  | 98  | 95  | 93  | 96  | 94  | 93  | 95  | 93  | 92  | 91  |  |  |   |
| 7   | 102 | 98  | 94  | 92  | 101 | 97  | 94  | 92  | 96  | 93  | 92  | 95  | 93  | 91  | 94  | 92  | 91  | 90  |  |  |   |
| 8   | 101 | 96  | 93  | 91  | 100 | 95  | 93  | 90  | 95  | 92  | 90  | 94  | 92  | 90  | 93  | 91  | 90  | 89  |  |  |   |
| 9   | 99  | 94  | 91  | 89  | 98  | 94  | 91  | 89  | 93  | 91  | 89  | 93  | 90  | 89  | 92  | 90  | 88  | 88  |  |  |   |
| 10  | 98  | 93  | 90  | 88  | 97  | 93  | 90  | 88  | 92  | 90  | 88  | 91  | 89  | 88  | 91  | 89  | 87  | 87  |  |  |   |

**AVERAGE LUMINANCE (cd/sqm):**

|     |         |
|-----|---------|
|     | 0°      |
| 0°  | 3049770 |
| 5°  | 1970544 |
| 10° | 555994  |
| 15° | 157205  |
| 20° | 65723   |
| 25° | 29112   |
| 30° | 14855   |
| 35° | 7863    |
| 40° | 3350    |
| 45° | 901     |
| 50° | 991     |
| 55° | 0       |
| 60° | 0       |
| 65° | 0       |
| 70° | 0       |
| 75° | 0       |
| 80° | 0       |
| 85° | 0       |

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°

Vertical Angle:  $50^\circ$

Luminance: 991 cd/sqm

TEST NUMBER: P1307255

CATALOG NUMBER: LDSQA3D17R129024DE010 3LSQPHRLD1MW

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 803.1  | 66.8      |
| 10°-20°   | 291.4  | 24.2      |
| 20°-30°   | 78.0   | 6.5       |
| 30°-40°   | 24.5   | 2.0       |
| 40°-50°   | 4.6    | 0.4       |
| 50°-60°   | 0.4    | 0.0       |
| 60°-70°   | 0.0    | 0.0       |
| 70°-80°   | 0.0    | 0.0       |
| 80°-90°   | 0.0    | 0.0       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| <hr/>     |        |           |
| 0°-30°    | 1172.5 | 97.5      |
| 0°-40°    | 1197.0 | 99.6      |
| 0°-60°    | 1202.0 | 100.0     |
| 0°-90°    | 1202.0 | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 1202.0 | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°    | Flux |
|-----|-------|------|
| 0°  | 17708 |      |
| 5°  | 11398 | 803  |
| 15° | 882   | 291  |
| 25° | 153   | 78   |
| 35° | 37    | 25   |
| 45° | 4     | 5    |
| 55° | 0     | 0    |
| 65° | 0     | 0    |
| 75° | 0     | 0    |
| 85° | 0     | 0    |
| 90° | 0     |      |

TEST NUMBER: P1307255

CATALOG NUMBER: LDSQA3D17R129024DE010 3LSQPHRLD1MW

**CANDELA DISTRIBUTION (FULL):**

| 0°    |         |
|-------|---------|
| 0°    | 17708.3 |
| 1°    | 17409.4 |
| 2°    | 16568.9 |
| 3°    | 15130.5 |
| 4°    | 13344.7 |
| 5°    | 11398.3 |
| 6°    | 9369.7  |
| 7°    | 7554.1  |
| 8°    | 5813.1  |
| 9°    | 4326.2  |
| 10°   | 3179.3  |
| 11°   | 2342.4  |
| 12°   | 1763.4  |
| 13°   | 1367.4  |
| 14°   | 1083.4  |
| 15°   | 881.7   |
| 17.5° | 560.4   |
| 20°   | 358.6   |
| 22.5° | 231.6   |
| 25°   | 153.2   |
| 27.5° | 104.6   |
| 30°   | 74.7    |
| 32.5° | 52.3    |
| 35°   | 37.4    |
| 37.5° | 26.2    |
| 40°   | 14.9    |
| 42.5° | 7.5     |
| 45°   | 3.7     |
| 47.5° | 3.7     |
| 50°   | 3.7     |
| 52.5° | 0.0     |
| 55°   | 0.0     |
| 57.5° | 0.0     |
| 60°   | 0.0     |
| 62.5° | 0.0     |
| 65°   | 0.0     |
| 67.5° | 0.0     |
| 70°   | 0.0     |
| 72.5° | 0.0     |
| 75°   | 0.0     |
| 77.5° | 0.0     |
| 80°   | 0.0     |
| 82.5° | 0.0     |
| 85°   | 0.0     |
| 87.5° | 0.0     |



TEST NUMBER: P1307255

CATALOG NUMBER: LDSQA3D17R129024DE010 3LSQPHRLD1MW

CANDELA DISTRIBUTION (continued):



(END OF REPORT)