

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P1306661

Luminaire Tested: LDSQA3D02R309024DE010 3LSQCDR1MB

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1306661
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2510-583-24)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LDSQA3D02R309024DE010 3LSQCDR1MB
Description: 3in Adjustable LED luminaire with, R30 optic, 2400K CCT AND, 90CRI , 3LSQCDR1MB TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 276.0 lumens
Efficiency: N/A
Efficacy: 76.7 lumens/watt
Spacing Criteria (0/90/45): 0.51 / 0.51 / 0.46
Luminous Opening: Rectangular (W 0.25' x L: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 3.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1306661
CATALOG NUMBER: LDSQA3D02R309024DE010 3LSQCDR1MB

Luminous Intensity Polar Plot



— 0°-180° - - 45°-225° - - - 90°-270°



TEST NUMBER: P1306661

CATALOG NUMBER: LDSQA3D02R309024DE010 3LSQCDR1MB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	102	102	102	100
1	115	113	111	110	113	111	109	108	107	106	105	103	102	101	100	99	99	99	99	99	97
2	112	108	105	103	109	106	104	102	103	101	99	100	99	97	98	96	95	95	94	94	94
3	108	104	100	97	106	102	99	97	100	97	95	98	95	94	95	94	92	92	91	91	91
4	105	100	96	93	103	99	95	92	97	94	91	95	92	90	93	91	89	89	88	88	88
5	102	96	92	89	101	95	92	89	94	91	88	92	90	87	91	89	87	87	86	86	86
6	99	93	89	86	98	92	89	86	91	88	85	90	87	85	89	86	84	84	83	83	83
7	96	90	86	83	95	90	86	83	89	85	83	87	85	82	87	84	82	82	81	81	81
8	94	88	84	81	93	87	83	81	86	83	80	85	82	80	84	82	80	80	79	79	79
9	91	85	81	78	91	85	81	78	84	80	78	83	80	78	82	80	78	78	77	77	77
10	89	83	79	76	88	82	79	76	82	78	76	81	78	76	80	78	76	76	75	75	75

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	184209	184209	184209
5°	179727	179951	180954
10°	153492	152775	151883
15°	94730	93606	93963
20°	35794	35995	35959
25°	11022	12067	11497
30°	4435	5628	4614
35°	1304	2397	1346
40°	540	967	540
45°	97	317	97
50°	0	54	0
55°	0	0	0
60°	0	0	0
65°	0	0	0
70°	0	0	0
75°	0	0	0
80°	0	0	0
85°	0	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 45°

Vertical Angle: 45°

Luminance: 317 cd/sqm



TEST NUMBER: P1306661

CATALOG NUMBER: LDSQA3D02R309024DE010 3LSQCDR1MB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	94.3	34.2
10°-20°	139.7	50.6
20°-30°	34.6	12.6
30°-40°	6.5	2.4
40°-50°	0.8	0.3
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	268.7	97.3
0°-40°	275.2	99.7
0°-60°	276.0	100.0
0°-90°	276.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	276.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1070	1070	1070	1070	1070	
5°	1040	1039	1041	1043	1047	94
15°	531	526	525	529	527	140
25°	58	62	64	63	60	33
35°	6	8	11	8	6	5
45°	0	1	1	1	0	0
55°	0	0	0	0	0	0
65°	0	0	0	0	0	0
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	0	0	0	0	0	0



TEST NUMBER: P1306661
 CATALOG NUMBER: LDSQA3D02R309024DE010 3LSQCDR1MB

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1069.6	1069.6	1069.6	1069.6	1069.6
1°	1070.1	1069.2	1069.2	1067.9	1070.3
2°	1066.2	1065.3	1066.8	1065.8	1068.8
3°	1060.4	1059.3	1061.5	1062.1	1063.6
4°	1051.8	1051.0	1053.3	1054.6	1058.7
5°	1039.6	1039.1	1040.9	1042.6	1046.7
6°	1022.8	1022.2	1023.3	1025.4	1028.0
7°	998.6	997.3	998.1	998.6	999.2
8°	967.9	966.0	964.9	967.2	968.5
9°	928.4	926.2	923.9	923.0	926.0
10°	877.7	874.5	873.6	871.5	868.5
11°	818.9	816.3	815.7	811.8	810.1
12°	751.5	750.2	751.7	749.4	748.5
13°	686.9	678.7	677.7	673.2	670.8
14°	610.5	603.0	602.8	600.4	603.6
15°	531.3	526.1	525.0	529.1	527.0
17.5°	338.7	342.2	341.3	339.2	335.5
20°	195.3	193.0	196.4	197.3	196.2
22.5°	104.1	105.0	105.6	108.2	109.9
25°	58.0	61.8	63.5	63.3	60.5
27.5°	36.1	38.4	41.6	39.5	37.1
30°	22.3	24.3	28.3	24.5	23.2
32.5°	12.0	15.2	18.2	15.2	12.5
35°	6.2	8.2	11.4	8.4	6.4
37.5°	4.1	4.7	7.3	4.7	4.1
40°	2.4	3.0	4.3	3.0	2.4
42.5°	1.1	1.7	2.4	1.7	1.1
45°	0.4	0.6	1.3	0.9	0.4
47.5°	0.0	0.2	0.6	0.2	0.0
50°	0.0	0.0	0.2	0.0	0.0
52.5°	0.0	0.0	0.0	0.0	0.0
55°	0.0	0.0	0.0	0.0	0.0
57.5°	0.0	0.0	0.0	0.0	0.0
60°	0.0	0.0	0.0	0.0	0.0
62.5°	0.0	0.0	0.0	0.0	0.0
65°	0.0	0.0	0.0	0.0	0.0
67.5°	0.0	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P1306661
CATALOG NUMBER: LDSQA3D02R309024DE010 3LSQCDR1MB

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)